



Enter Your Keywords



SOLUTIONS   PRODUCTS   DESIGN SUPPORT   BUY & SAMPLE   ABOUT CYPRESS

Home > Products > CY8C4125AZA-M443

## CY8C4125AZA-M443



Status: In Production

Product Specs	Pricing & Inventory	Packaging/Ordering	Quality and RoHS	Technical Documents
CY8C4125AZA-M443				DESIGN SUPPORT
Automotive Qualified	Y			Development Kits
CPU Core	ARM Cortex-M0			Forums
CapSense	Y			Knowledge Base
Dedicated ADC (#Max Resolution @ Sample Rate)	SAR (1, 12-bit @ 806 ksp/s)			Packaging
EEPROM (KB)	0			Product Brochures
Flash (KB)	32			Quality & Reliability
JTAG and Si ID	0x1180			Samples
LCD Direct Drive	Y			Technical Support
Max. Operating Frequency (MHz)	24			Technical Training
Max. Operating Temp. (°C)	85			Third Party Network (CYPros)
Max. Operating Voltage (V)	5.50			
Min. Operating Temp. (°C)	-40			
Min. Operating Voltage (V)	1.71			
No. of CAN Controllers	0			
No. of Continuous Time Blocks	1			
No. of DMA Channels	8			
No. of Dedicated Comparators	2			
No. of Dedicated Timer/Counter/PWM Blocks	8			
No. of GPIOs	38			
No. of Op Amps	2			
No. of SIO	0			
No. of Serial Communication Blocks	4			
No. of USB IO	0			
No. of Universal Analog Blocks	0			
No. of Universal Digital Blocks	0			
PLL	N			
SRAM (KB)	4			
Series	PSoC 4100M			
Tape & Reel	N			
USB (Type)	None			

PRICING & INVENTORY AVAILABILITY					
1-9 unit Price*	10-24 unit Price*	25-99 unit Price*	100-249 unit Price*	250-999 unit Price*	1000+ unit Price*
Contact Sales					

Availability	Quantity	Ships In	Buy from Cypress	Buy from Distributors
Out of Stock	0	Please click <a href="#">here</a> to check lead times	Contact Sales	Contact Sales

\* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku

PACKAGING/ORDERING	
Package	TQFP
No. of Pins	44
Package Dimensions	275 L x 1.4 H x 275 W (Mils)
Package Cross Section Drawing	Download
Package Carrier	TRAY
Standard Pack Quantity	250
Minimum Order Quantity (MOQ)	250
Order Increment	250
Estimated Lead Time (days)	91
HTS Code	8542.31.0001
ECCN	(A.3)
ECCN Suball	3A991.A.3

QUALITY AND ROHS	
Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	Y Print RoHS Certificate of Compliance
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au
Marking	Cypress Marking Format

<b>Device Qualification Reports</b>
FIT/MTBF, ESD (HBM/CDM) and Latch-up data available in the Device Qualification Report.
QTP#162707: AUTOMOTIVE PSoC 4100M and PSoC 4200M DEVICE FAMILY S8PFHD-10P, FAB25 (AL BEOL INTERCONNECT).pdf <i>Last Update: Mar 06, 2019</i>

TECHNICAL DOCUMENTS
<b>Application Notes (17)</b>
AN84858 - PSoC®4 Programming Using an External Microcontroller (HSSP) Jan 19, 2020
AN93637 - PSoC® 4 Sensorless Field-Oriented Control (FOC) Dec 30, 2019
AN82156 - PSoC® 3, PSoC 4, and PSoC SLP - Designing PSoC Creator™ Components With UDB Datapaths Oct 02, 2019
AN82250 - PSoC Creator - Implementing Programmable Logic Designs with Verilog Sep 22, 2019
<a href="#">Show More</a> ▼

### SOLUTIONS

Automotive  
Industrial  
Consumer

### PRODUCTS

Wireless  
Microcontrollers (MCUs)  
Memory  
Universal Serial Bus (USB)  
Power Management  
Touch Sensing  
Clocks & Buffers

### DESIGN SUPPORT

Community  
Videos  
Quality & Reliability  
Product Roadmaps

### ABOUT US

Investors  
Careers

#### CORPORATE HEADQUARTERS

Cypress Semiconductor Corp.  
198 Champion Court  
San Jose, CA 95134 USA  
Tel: +1-408-943-2600

#### CUSTOMER SERVICE SUPPORT

+1-800-541-4736  
Hours:  
8:00AM - 5:00PM (local time)  
Create a MyCase  
Cypress Developer Community

#### INTERNATIONAL SUPPORT

+1-408-943-2600  
United States +1-800-541-4736  
Hours:  
4:30AM - 1:30PM (pacific time)  
7:30PM - 4:30AM (standard time)

#### OTHER REQUESTS

Contact Us  
Report a Website Problem  
Report a Security Vulnerability

[ABOUT US](#)   [CAREERS](#)   [INVESTORS](#)   [LEGAL](#)

