



PART NAME: KNOB		SCALE: 1:1	DATE: 5/30/17	DR. BY JD		DESIGNERS & MANUFACTURERS OF KNOBS, HANDLES, CASES & CUSTOM PLASTIC COMPONENTS	P/N	3022BG																			
THIS DRAWING IS THE PROPERTY OF DAVIES MOLDING COMPANY. IS SUBMITTED SOLELY AS A DESIGN OR ENGINEERING PROJECT. WE ACCEPT NO RESPONSIBILITY WHATSOEVER FOR THE PRACTICAL APPLICATION OF THE PIECES MADE TO THIS DESIGN.							M/NO.	1475																			
<table><tr><td>CAVITY</td><td>3022</td></tr><tr><td>PLUNGER</td><td>3022</td></tr><tr><td>PLUNGER PIN</td><td>3022</td></tr><tr><td>OUTER PIN</td><td>3025-3</td></tr><tr><td>INNER PIN</td><td>3025HQ</td></tr><tr><td>SHIMS</td><td>.250+.250+.047</td></tr><tr><td>PIN BAR</td><td>1475</td></tr><tr><td>INSERT</td><td>2508</td></tr><tr><td>PLUNGER KEY</td><td>1/4x1/4x7/16</td></tr><tr><td>CAVITY KEY</td><td>1/4x1/4x1/2</td></tr></table>								CAVITY	3022	PLUNGER	3022	PLUNGER PIN	3022	OUTER PIN	3025-3	INNER PIN	3025HQ	SHIMS	.250+.250+.047	PIN BAR	1475	INSERT	2508	PLUNGER KEY	1/4x1/4x7/16	CAVITY KEY	1/4x1/4x1/2
CAVITY	3022																										
PLUNGER	3022																										
PLUNGER PIN	3022																										
OUTER PIN	3025-3																										
INNER PIN	3025HQ																										
SHIMS	.250+.250+.047																										
PIN BAR	1475																										
INSERT	2508																										
PLUNGER KEY	1/4x1/4x7/16																										
CAVITY KEY	1/4x1/4x1/2																										
																											
MATERIAL: G.P. PHENOLIC (B11) COLOR: BLACK																											
<table><tr><td>TOLERANCES: UNLESS OTHERWISE SPECIFIED</td><td>DO NOT SCALE DRAWING</td><td></td><td></td></tr><tr><td>DECIMALS: X.XXX ± .005 X.XX ± .015</td><td>MM: X.XX ± 0.15MM X.X ± 0.4MM</td><td></td><td></td></tr><tr><td>FRACTIONS ± 1/64</td><td>ANG. ± 1°</td><td colspan="2">CHANGES</td></tr></table>								TOLERANCES: UNLESS OTHERWISE SPECIFIED	DO NOT SCALE DRAWING			DECIMALS: X.XXX ± .005 X.XX ± .015	MM: X.XX ± 0.15MM X.X ± 0.4MM			FRACTIONS ± 1/64	ANG. ± 1°	CHANGES									
TOLERANCES: UNLESS OTHERWISE SPECIFIED	DO NOT SCALE DRAWING																										
DECIMALS: X.XXX ± .005 X.XX ± .015	MM: X.XX ± 0.15MM X.X ± 0.4MM																										
FRACTIONS ± 1/64	ANG. ± 1°	CHANGES																									