





W4E330A Series

Axial

Ø 330mm S-Range

- ebm-papst offers a wide range of AC axial fans to optimally fit any application.
- All metal construction, shallow profile, round venturi plate. Reduced noise and highly efficient compared to other fans.
- Mounting plate with 9 mm holes. Ready to install.
- Discharge over struts: Dir. of rotation is CCW looking at rotor.
- Inlet over struts: Dir. of rotation is CW looking at rotor.
- Maintenance-free ball bearings.
- UL, CSA, VDE approvals on most models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Grill Position	Wgt. (lbs)
W4E330-CP22-70	2	1840	115	50/60	145	63	40	Ball	Leads	14	Dischg	5.51
W4E330-CP22-71	2	1840	115	50/60	145	63	40	Ball	Leads	14	Inlet	5.51
W6E330-CP02-70	1	1295	230	50/60	72	54	70	Ball	Leads	2	Dischg	5.51
W6E330-CP02-71	1	1295	230	50/60	72	54	70	Ball	Leads	2	Inlet	5.51
W4E330-CP18-70	2	1840	230	50/60	145	63	40	Ball	Leads	4	Dischg	5.51
W4E330-CP18-71	2	1840	230	50/60	145	63	40	Ball	Leads	4	Inlet	5.51



ebm-papst

e-mail: sales@us.ebmpapst.com · TEL: 860-674-1515 · FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2006 © ebm-papst Inc. reserves the right to change any specifications or data without notice