



Parallel Protection Plug: To Plug .580 in (14.7 mm) Hole, 12.5 mm (0.492 in) Plug Height

Item Code: 12675A

Black PVC Parallel Protection Plug with a fitting diameter of .580 in (14.7 mm) are easily applied to protect connectors and provide a clean finish.

In Stock

Description		Quantity	Unit Price	Options
Fitting Diameter	: .580 in (14.7 mm)	Standard Pack: 6000		1
Fitting Height	: 12.5 mm (0.492 in)	Order any quantity		
Flange Thickness	: 1.5 mm (0.059 in)	1	: \$1.5336	Add to Cart Free Sample Request Quote
Inside Diameter	: 12.2 mm (0.48 in)	600	: \$0.769	
Fitting Style	: Push Fit	1200	: \$0.3067	
Color	: Black	6000	: \$0.1368	
Material	: PVC	30000	: \$0.1291	
Full Material	: Polyvinyl Chloride	60000	: \$0.1225	
		90000	: \$0.1159	
		120000	: \$0.109	



Print Page

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



About Us

[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)
[Knowledge Center](#)

Customer Service

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

Policies

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

Terms of Use

[Website Terms of Use](#)
[Cookie Policy](#)



ABOUT SSL CERTIFICATES