






TOL ± 0.05 [.002] UNLESS NOTED



OPERATING TEMPERATURE: 0°C TO 70°C

CT P1 P4 P2 P3 P5 P6

CT P3 P5 P6

GND P8

J1 J2 J3 J6

J4.5 J7.8

1000pF/2KV 4X 75 W

Class	MAXMJ
-------	-------

Copyright by ERNI GmbH

b
Rev

02JUL04
Date