



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Bussmann series military fuse

**F03A250V2AS**

**UPC:**051712157179

### Dimensions:

- **Height:** .001 IN
- **Length:** .001 IN
- **Width:** .001 IN

**Weight:**.1 LB

### Warranties:

- Not Applicable

### Specifications:

- **Type:** Electronic, Fast-acting
- **Amperage Rating:** 2A
- **Voltage Rating:** 250 Vac, 125 Vdc
- **Interrupt Rating:** 100 AIC at 250 Vac, 10 kAIC at 125 Vac/dc
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Diameter:** .25 IN
- **Connection:** Ferrule end X ferrule end
- **Service Response Time:** 4 hour minimum at 100%, 60 minute maximum at 135%, 120 second maximum at 200%

### Supporting documents:

- [Product Catalog](#)

**Certifications:** No Data

### Product compliance:

- Contact factory

