






 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances siehe / see IEC 603-2		
				Dat.	Name	Maßstab/Scale 1 : 1 (2 : 1)	Bauform B Messerleiste Einlöt , 32 pol. <i>type B male connector</i> <i>solder , 32 pol.</i>	
			Detail.	11.07.00	Rie.			
			Insp.	11.07.00	Pa.			
			Stand.					
			HARTING KGaA				TB 09 02 132 x931	
28027			D-32339 ESPELKAMP					
Mod.	Dat.	Name				Sub.	Blatt/ page 	

09 02 132 6931
Printed board connector

Other applications

Type	Type B
Standard/Inverse	Standard
Contact gender	Male contacts
Size	Whole size
Number of contacts	32 poles
Contact arrangement	Row a
Termination	Angled solder pins
Termination length	3.0 mm
First mating contact	without first mating contacts
Performance Class	Performance level 2 as per IEC 60603-2
Contacts	with contacts
Row pitch	2.54 mm
Board fixing	Without fixing
Current	2 A max.
Clearance/Creepage	1.2 / 1.2 mm min.

Inquiry

Data sheets are available in following formats
2D files

PDF

DXF

09 02 132 2931
Printed board connector

Other applications

Type	Type B
Standard/Inverse	Standard
Contact gender	Male contacts
Size	Whole size
Number of contacts	32 poles
Contact arrangement	Row a
Termination	Angled solder pins
Termination length	3.0 mm
First mating contact	without first mating contacts
Performance Class	Performance level 1 as per IEC 60603-2
Contacts	with contacts
Row pitch	2.54 mm
Board fixing	Without fixing
Current	2 A max.
Clearance/Creepage	1.2 / 1.2 mm min.



Data sheets are available in following formats

2D files

Typenblatt

Typenblatt

09 02 132 7931
Printed board connector

Other applications

Type	Type B
Standard/Inverse	Standard
Contact gender	Male contacts
Size	Whole size
Number of contacts	32 poles
Contact arrangement	Row a
Termination	Angled solder pins
Termination length	3.0 mm
First mating contact	without first mating contacts
Performance Class	Performance level 3 as per IEC 60603-2
Contacts	with contacts
Row pitch	2.54 mm
Board fixing	Without fixing
Current	2 A max.
Clearance/Creepage	1.2 / 1.2 mm min.

Inquiry

Data sheets are available in following formats

2D files

PDF

DXF