

HOME &gt; Product Info

## Product Category

## Product Info

## 1 Products

	1-1	
Product No.	MSS-LP-1.5(40)	
HRS No.	319-0007-9 40	
Status	In Production	
RoHS	Yes	
Series	MSS	
Category	Coaxial Connectors	
No. of Positions	N/A	
Contact Mating Area Plating	Gold	
Contact Gender	Male	
Connector Type	Cable	
PCB Mount Type	N/A	
Current Rating(Amps)(Max.)	N/A	
Impedance (ohm)	50	
Frequency (GHz)(Min)	0	
Frequency (GHz)(Max)	1	
V.S.W.R. (Max)	N/A	
Termination Style	Soldering	
Temperature (deg C)	-30 to 60	
Mating/Unmating Cycles	3000	
Applicable Cable	1.5D2V	
Generic Name	N/A	
Selling Unit	1pcs.(1pcs.)	
General Description	Plug; Right angle; Pushpull lock	
Inquiry	<a href="#">REQUEST</a>	
Similar Products	<a href="#">Similar Products ▶</a> 3 products	
e-Commerce	<a href="#">E-Commerce ▶</a>	
Product No.	MSS-LP-1.5(40)	
HRS No.	319-0007-9 40	
	1-1	

[▶ Terms of Service](#)
[▶ RoHS](#)