

HOME > Product Info

Product Category

Product Info

1 Products

	1-1	
Product No.	BNC-R-PC-2(40)	
HRS No.	302-0243-0 40	
Status	In Production	
RoHS	Yes	
Series	BNC	
Category	Coaxial Connectors	
No. of Positions	N/A	
Contact Mating Area Plating	Silver	
Contact Gender	Female	
Connector Type	Board mounting	
PCB Mount Type	Throughhole	
Current Rating(Amps)(Max.)	N/A	
Impedance (ohm)	50	
Frequency (GHz)(Min)	0	
Frequency (GHz)(Max)	2	
V.S.W.R. (Max)	1.2	
Termination Style	N/A	
Temperature (deg C)	-55 to 85	
Mating/Unmating Cycles	5000	
Applicable Cable	N/A	
Generic Name	N/A	
Selling Unit	1pcs.(1pcs.)	
General Description	Receptacle; Bayonet lock coupling	
Inquiry	REQUEST	
Similar Products	Similar Products ▶ 2 products	
e-Commerce	E-Commerce ▶	
Product No.	BNC-R-PC-2(40)	
HRS No.	302-0243-0 40	
	1-1	

[▶ Terms of Service](#)
[▶ RoHS](#)