




REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED	12/14/05
A	CHANGE x AND y's	3/21/06
B	MOL TO 9.6, ADD FLUX NOTE	4/10/06



PC BOARD PUNCH PATTERN
BOARD THICKNESS 1.6±0.1mm.
(NO APPLICATION OF FLUX, SHALL BE DONE.)

JKL PART NUMBER: CNW5-CW11/GRA/39-01-6M/S

LAMP NUMBER: CW11**

VOLTS RATED	AMPS ± 10%	*MSCP ± 25%	*LUMENS ± 25%	AVERAGE LIFE HRS.	FILAMENT TYPE
14.0	.065	.200	2.51	5,000 D.C.	C-2F

*LAMP RATING ONLY WITHOUT BASE AND FILTER.

**LAMP GLASS LEAD (Pb) FREE.

***PLATING LEAD (Pb) FREE.

CONTACT JKL FOR LEAD (Pb) FREE LOT IDENTIFICATION.

FILTER NUMBER: 39-01-6M/S

BASE COLOR: GRAY

COLOR COORDINATES (SPHERE)

x = .365 ± .025

y = .345 ± .025

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.3 2 PL +/- 0.30 ANGLE +/- 0		JKL COMPONENTS CORPORATION						
				TITLE						
				T-1 NEO-WEDGE BASED LAMP WITH FILTER						
DRAWN BY L. WENGSTROM		APPV'D BY LEN		DATE 4/10/06		SIZE A	FSCM NO. 55335	DRAWING NO. CNW5-CW11/GRA/39-01-6M/S		
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED						SCALE NONE	RELEASED DATE 12/14/05	REVISION DATE 4/10/06	REV. NO. B	SHEET 1 OF 1