


DIMENSIONS: mm



SPECIFICATIONS

Wire:	AWG #26
Black & Red:	150MM±5MM
Strip & Tin:	5MM±1MM
Holder:	Abs Resin, Black Color
Contact:	0.25 MM Thick Spring Steel Nickel Plated
RoHS Compliant	