



Technical drawing showing two holes in a part. The left hole is labeled "Aufnahmeloch Fixierzapfen" (location hole fixing pin) and the right hole is labeled "für Fixierzapfen" (for fixing pin). Dimensions include diameters of 3.1 and 3.5, a distance of 9 ± 0.05 between hole centers, and a 0.2 x 45° chamfer on the right hole. Surface texture symbols are present on the top and bottom surfaces.




2 schwarz / *black*
4 blau / *blue*
1 braun / *brown*




Schutzart nach EN 60529 IP 67
protection according to EN 60529 IP 67

Herstelljahr / Woche nach DIN EN 60062
year of production / week acc. DIN EN 60062



Leitung DIN 72551-FLRY-0.35-A-schwarz (Anschl. 2)
lead DIN 72551-FLRY-0.35-A-black (connection 2)



										1068.0601-02											
										Art.-PT ITEM-PI											
fuer Form und Lage FOR SHAPE AND LOC. fuer Winkel FOR ANGLE				Allgemeintoleranzen UNTOLERANCED DIMENSIONS						Pause COPY		Blatt SHEET 01		Typ K		Zeichn./DRAWING NO. 10680601		Index e			
				PROJEKTION 		Abmasse und Nennmassebereiche		Laengen LENGTH												Radien RADI	
						Angaben in mm		0-6 ± 0.1 ± 0.1												± 0.1	
								>6-15 ± 0.2 ± 0.2												± 0.2	
																				>15-30 ± 0.2 ± 0.2	
						>30-70 ±															
						>70-120 ±															
						>120-200 ±															
</																					