








UFT Cartridges are compatible with CV-500 and CV-5200 Systems –CV-H4-UFT Hand pieces

Temperature	UFT	Application
675°F/357°C	UFT-6	Temperature Sensitive
775°F/412°C	UFT-7	Most Standard

Please note the above temperatures are the maximum temperatures of the heater. The idle temperature is dependent on the geometry of the cartridge (up to 15°C lower.)

Chisel		
	UFT-6CH9006S	CHISEL 0.6mm x 9mm (.024" x .035")
	UFT-7CH9006S	
	UFT-6CH9008S	CHISEL 0.8mm x 9mm (.031" x .035")
	UFT-7CH9008S	

Conical		
	UFT-6CN5502R	CONICAL, BENT 0.2 mm x 5.6 mm (0.008" x 0.220")
	UFT-7CN5502R	
	UFT-6CN5504R	CONICAL, BENT 0.4 mm x 5.6 mm (0.16" x 0.220")
	UFT-7CN5504R	
	UFT-6CN8004S	CONICAL 0.4 mm x 8.7mm (0.16" x 0.343")
	UFT-7CN8004S	

Power Wedge		
	UFT-6PW3150S	POWER WEDGE 0.31mm x 5.0mm (0.012" X 0.196")
	UFT-7PW3150S	
	UFT-6PW2954C	POWER WEDGE 0.29mm x 5.4mm (0.011" X 0.213")
	UFT-7PW2954C	