

MOMENTARY ACTION NORMALLY OPEN OR NORMALLY CLOSED



Features:

- MIL-PRF-8805/96 approved
- Momentary snap-action
- Sealed or unsealed
- Compact, space-saving design
- Black or red button colors available
- Clear or black case colors available
- RoHS/WEEE/Reach compliant

Standard Characteristics/Ratings:

ELECTRICAL RATINGS:

Load Sea Level @ 28VDC or 115VAC, 60/400Hz

Resistive 5A

Inductive 2A

DWV 1000Vrms

Electrical Life: 25,000 cycles

Mechanical Life: 50,000 cycles

Seal: Unsealed per MIL-PRF-8805 Design 1
or Dusttight per MIL-PRF-8805 Design 2

Operating Temp Range: -55°C to +85°C

Operating Force: 1.5 lbs. +/- 0.5 lb. (unsealed)
1.75 lbs. +/- 0.5 lb. (dusttight)

Total Travel: 0.095 inches +/- 0.015 inches

Overtravel: 0.010 inches min

Pretravel: 0.010 inches min

MATERIALS:

Case: Anodized aluminum alloy, clear or black

Button: Thermoplastic

Terminals: Silver alloy

Mounting Hardware: Hex nut and lockwasher

Momentary, Normally Open

OTTO PART NUMBER	MILITARY PART NUMBER	SEAL	CASE COLOR	BUTTON COLOR
PE-1111	M8805/96-001	UNSEALED	CLEAR	RED
PE-1112	M8805/96-002	UNSEALED	CLEAR	BLACK
PE-1121	M8805/96-005	UNSEALED	BLACK	RED
PE-1122	M8805/96-006	UNSEALED	BLACK	BLACK
PE-1211	M8805/96-009	DUST TIGHT	CLEAR	RED
PE-1212	M8805/96-010	DUST TIGHT	CLEAR	BLACK
PE-1221	M8805/96-013	DUST TIGHT	BLACK	RED
PE-1222	M8805/96-014	DUST TIGHT	BLACK	BLACK

Momentary, Normally Closed

OTTO PART NUMBER	MILITARY PART NUMBER	SEAL	CASE COLOR	BUTTON COLOR
PE-2111	M8805/96-003	UNSEALED	CLEAR	RED
PE-2112	M8805/96-004	UNSEALED	CLEAR	BLACK
PE-2121	M8805/96-007	UNSEALED	BLACK	RED
PE-2122	M8805/96-008	UNSEALED	BLACK	BLACK
PE-2211	M8805/96-011	DUST TIGHT	CLEAR	RED
PE-2212	M8805/96-012	DUST TIGHT	CLEAR	BLACK
PE-2221	M8805/96-015	DUST TIGHT	BLACK	RED
PE-2222	M8805/96-016	DUST TIGHT	BLACK	BLACK

