

Search within category

GO

BUY NOW

DESIGN / INSTALL



PV8-10RX-TY

Ring Terminal, large wire, 8 AWG, #10 stud size, vinyl expanded insulation, bulk package.
PV8-10RX-TY replaces PV8-10RX-T

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Note	PV8-10RX-TY replaces PV8-10RX-T
Product Type	Loose Piece Ring Terminal
Stud Size	#10
Wire Range	8 AWG
Wire Range (mm²)	10
Barrel Configuration	Expanded Entry
Barrel Type	Insulation Support, Brazed Seam
Base Material	Copper
Insulation	Vinyl
Panduit Color Code	Red
Plating Type	Tinned
Part Number Series	PV-RX
Clearance	0.43
Clearance (mm)	10.9
Length (In.)	1.52
Length (mm)	38.6
Max. Insulation Diameter In. (mm)	0.36 (9.1)
Stock	0.04
Stock (mm)	1.0
Width (In.)	0.47
Width (mm)	11.9
Wire Strip Length (In.)	3/8" (.375)
Wire Strip Length (mm)	9.5
Flammability Rating	UL 94V-0
Max. Voltage Rating	600 V
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
CA-800/EZ Series Crimp Die	—
CA9 Series Crimp Die	—
Tool	CT-720 With Die Insert CD-720PV8-2, CT-2600 With Die Insert CD-2600-PV8

CSA Certified	C22.2 No. 65
Mil. Std. Part Number	—
UL Listed	UL486A-486B
Packaging Type	Box
Part Features	• Expanded wire entry designed to accommodate wire with a larger insulation thickness • Ring tongue design assures a secure connection in high vibration applications • Insulation support helps to prevent wire damage in bending applications • Internal barrel serrations assure good wire contact and maximum tensile strength
RoHS Compliancy Status	Compliant
Min. Order Qty.	200.0000