



Search within category

GO

BUY NOW

DESIGN / INSTALL



F9UYPF5F5AAF047

24-Fiber OS2 HD Flex Indoor Small Diameter Trunk, Plenum, 24F MPO Male to 24F MPO Male, Method A, Std IL, Pulling Eye, 47 Feet, Yellow.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	10G fiber backbone or permanent link
Cable Color	Yellow
Connector 1 Type	24F MPO Male
Connector 2 Type	24F MPO Male
Fiber Count	24
Fiber Type	OS2
Flammability Rating	Plenum (OFNP)
Length (ft.)	47
Length (m)	14.33
Part Features	Minimize waste, optimize cable management, speed deployment, improve flexibility and manageability for lower installation costs.
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000