

### Samples Request

## Browse by Application

Share

Enter part number or keyword

### Search Options

1 Result(s): [ All ] - 12004917

 Compare

12004917 - Contact Lamp Socket Female




☐ Unsealed Tin Plating Terminal, Cable Range  
0.50 - 1.00 mm<sup>2</sup>

Compare



Part # 12004917

Question about this product?

Attributes	Documents (2)
Part # :	12004917
Description :	Contact Lamp Socket Female Unsealed Tin Plating Terminal, Cable Range 0.50 - 1.00 mm2
Product Type :	Terminal
Status :	 Active
Terminal Family :	LP SOC
Series :	CONTACT
Gender :	Female
Sealable :	Unsealed
Weight [g] :	1
Plating :	Tin
Minimum Cable Diameter [mm] :	2.03
Maximum Cable Diameter [mm] :	3.52
Minimum Cable Core Cross Section [mm2] :	0.50
Maximum Cable Core Cross Section [mm2] :	1.00
RoHs compliant :	 Yes
ELV compliant :	 Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.