

building a smarter, unified business foundation

[CHANGE]

REGISTER / LOG IN

FOLLOW US

PANDUIT

SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO

Search within category

GO

BUY NOW

DESIGN / INSTALL

Specs

Documents

★ Add to Favorites

Add to BOM

Std. Pkg. Qty.	100
Product Type	Cable Tie Mounts - Through Panel Hole
Mounting Method	Push Barb
Environment	Indoor
Flammability Rating	V-2
Material	Nylon 6.6
CE Compliant	Yes
UL Recognized	E136577
Max. Panel Thickness (In.)	0.13
Max. Panel Thickness (mm)	3.2
Panel Hole Diameter (In.)	0.250
Panel Hole Diameter (mm)	6.4
Height (In.)	0.33
Height (mm)	8.4
Length (In.)	0.42
Length (mm)	10.7
Width (In.)	0.16
Width (mm)	4.1
Color	Natural
Max. Continuous Use Temperature	185°F (85°C)
RoHS Compliancy Status	Compliant
Min. Order Qty.	100.0000

PBMS-H25-C

Push button cable tie mount, .25" (6.4mm) hole, natural, standard package.

Unified Physical Infrastructure

LEGAL INFORMATION

PRIVACY POLICY

CONTACT US

SITE MAP

WHERE TO BUY

JOBS

UNSUBSCRIBE