



RF SWITCHES

R-MCX SERIES



part number	captive center contact	dimensions		panel	mounting	finish	packaging
		A	B				
R299 137 800	yes	6	2,7	P01	M02	Gold	200/reel
R299 137 800W	yes	6	2,7			Gold	unit
R299 137 801	yes	6	2,7			Gold	900/reel
R299 142 821	yes	4,8	1,45			Gold	900/reel
R299 142 822	yes	4,8	1,45			Gold	100/reel
R299 142 822W	yes	4,8	1,45			Gold	unit

COMPATIBLE PLUGS CRIMP TYPE FOR FLEXIBLE CABLES




Fig. 1




Fig. 2

cable	part number	fig	captive center contact	finish	packaging	note
2,6/50/S	R299 138 000	1	yes	Gold	unit	straight plug
	R300 113 100	2	yes	Gold	100	right angle plug

R-MCX / SMA ADAPTER

part number	Designation
R191 977 020	R-MCX female - SMA male

Test boards available upon request, please contact us.