



Continuous Rating	100A 32VDC Max.	Mounting Hole 	Circuit Diagram	
Intermittent Rating	150 Amps		OFF	ON
Cranking Rating	500 Amps 5 sec.			
Contact Resistance	50m ohm Max			
Insulation Resistance	DC 500V 100M ohm Min			
Dielectric Strength	AC 1000V 1 minute, DC 2000V 1 minute			
Operation Temperature	-30°C~+60°C			
Switch Function	2P SPST OFF-ON			

Actuator can't be taken out



***MATERIAL:**

Housing: Black, PA#66+33%GF
with White hot stamping

Actuator: Red, PBT+15%GF

Name Plate: White, ABS
with Black hot stamping



Bottom: Black, PBT+15%GF

Nut: Black, PA#66

Bolt: Brass

Hex Nut: Ni-plated, Brass

1 NUT ASSY



tolerances Unless otherwise specified ± 0.3

C3\WORK14\A23-7A

05/27/'16	曹盈芳	依營業Judy要求, 加高本體隔板高度				△	
Date	Name	Descriptions				NO	
Drawn	Checked	Approved	SCI BOM No.	1340050	Model Name	Battery SWITCH	
曹盈芳		王伯山	Customer No.		Model No.	A23-7A	REV.
05/27/'16		5/20/16	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		1