





Continuous Rating	50Amps 50VDC Max.	Mounting Hole  Panel Thickness:9.5mm Max.	Circuit Diagram	
Intermittent Rating	75 Amps		OFF	ON
Cranking Rating	300 Amps 5 sec.		 	
Contact Resistance	50m ohm Max			
Insulation Resistance	DC 500V 100M ohm Min			
Dielectric Strength	AC 1000V 1 minute, DC 2000V 1 minute			
Operation Temperature	-30°C~+60°C			
Switch Function	2P SPST OFF-ON			

Actuator can't be taken out



***MATERIAL:**

Housing: Black, PA#66+33%GF

Actuator: Red, PBT+15%GF

Name Plate: White, ABS





with black hot stamping

Bottom: Black, PBT+15%GF

Nut: Black, POM

Screw: Ni-plated, Brass

1 HEX NUT ASSY



tolerances Unless otherwise specified ± 0.3

C3/WORK14/A23-6

									△
									△
Date	Name	Descriptions							NO
Drawn	Checked	Approved	SCI BOM No.	1340049	Model Name	Battery SWITCH			
B.S.Wang		王偉山	Customer No.		Model No.	A23-6A			REV.
2/25/16		3/31/16	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				0