







Rating	3A 125V AC, 1.5A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Switch Function	2P SPST OFF-(ON)		




Material:
Frame: Black, Nylon#66
Actuator: Red, ABS
Base: Black, NYLON#66+15%GF



卡扣結構

Tolerances ± 0.3 Unless Otherwise Specified

								△
								△
Date	Name	Description						NO
Drawn	Checked	Approved	SCI BOM NO	183129 4	Model Name	PUSH SWITCH		
Ruby			Customer No.		Model No.	R13-23A-05-BR	Rev.	
6/19/14		3/24-15	Unit	mm	Ⓢ Shin Chin Industrial Co., Ltd.		0	