







Rating	3A 125V AC, 1.5A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Switch Function	2P SPST OFF-(ON)		

Material:
Housing: Brass Alloy, Cr-Plating
Button: Black, Nylon#66
Bottom Cover: Black, PBT+30%GF
Printed: None



For 玖新
Tolerances Unless Otherwise Specified ± 0.3

								△
								△
Date	Name		Description					No.
Drawn	Checked	Approved	SCI BOM No.	1830830	Model Name	PUSH SWITCH		
曹盈芳			Customer No.	112-R13-502MA-B/B	Model No.	R13-502MA-05	Rev.	0
07/29/14		7/28/14	Unit	mm	Shin Chin Industrial Co., Ltd.			