





NOTES:


- 1) CAPACITANCE (1000hrs.): 1000pF
- 2) CAP TOLERANCE: $\pm 20\%$
- 3) DISSIPATION FACTOR: 4% MAX.
- 4) INSULATION RESISTANCE: 25°C 1G Ω M
- 5) 200 VDC RATED @ +125°C
- 6) DIELECTRIC WITHSTANDING VOLTAGE: 700 VDC
- 7) CURRENT RATING: 10 AMPS
- 8) REFLOW TEMPERATURE LIMIT: +235°C FOR 5 SEC.
- 9) PACKAGING: TAPE & REEL (500 OR 2000 PCS.)

MARKING:

PART: NONE
 PACKAGE: PART NO.
 SCI DATE CODE
 QTY.



MIDDLE TERMINAL



										01	00	REV. NO.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES (mm). DO NOT SCALE.	TOLERANCES UNLESS OTHERWISE SPECIFIED Fractions $\pm 1/64$ Dec. .xx $\pm$.01[0.254] Dec. .xxx $\pm$.005[0.127] Angles $\pm 0^\circ 30'$	 FAIRVIEW PENNSYLVANIA Description SURFACE MOUNT FILTER Engr. B. DEVINE Sheet 1 of 2
										CN 44620-ENG	CN 27964-CPD	CHANGE NOTICE			

Quality Products From The Specialists In Electro-Magnetic Compatibility

[illegible]