## VIDEO PATCH CORDS

Switchcraft new broadcast series video patch cords are available in eight base ten color codes. Our cable is a high performance serial digital 75 Ohm RG59 type. This unique low-loss cable is ideal for "True" 75 Ohm HD patching as well as conventional analog signals.

The jacket is made flexible with very low retract memory.

## **FEATURES:**

- \* Rugged nickel-plated handles knurled for positive finger grip.
- \* Flexible black "boot" placed on all cable colors for more positive grip and cable strain relief.
- \* Overall flexible jacket for easy coil and low retract memory.

## SPECIFICATIONS:

Plug Housing: Plug Contact Pin: Nickel-plated, copper alloy. Gold-plated, copper alloy.

Cable:

22 AWG (19 x 34) Stranded BC

Shield:

95% BC Braid

Dielectric:

Conductor:

.146", 3.70mm, Cellular

(Foam) PE

Jacket:

Matte Finish PVC

Nom. Imp:


75 Ohm

VP			VMP	AND DESIGNATION OF SELECTION OF	
Video	Length	Cable	Video	Length	Cable
Patch	(Feet)	Color	Patch	(Feet)	Color

Part Numbering System Video Patch Cords	Video Patch	Length (Feet)
Standard .090 WECO	VP	niell-FT ne beau bet
Midsize Video Patch	VMP	e -3 reiw au ldropoa

Colors		Color Code	Stock Lengths
time print.	oid morning	on to bebeen t	o min 19vokason
Black	=	BK	2' 0
Red	=	R	3'
Orange	=	0	8 mone4' 10777
Yellow	=	Y	5' e0 TT
Green	=	GN	6'
Blue	=	BL	7'
Purple	=	P	8'
Gray	=	GY	9'
			10'

(Custom lengths are available by request)





DIMENSIONS ARE FOR REFERENCE ONLY

Inch