

TK010HM00

Item	Specification (subject to change)
Communicaton Scheme	Bluetooth ver. 4.0 (Class2) , USB
Max. Communication Distance	Max. app. 10m
Frequency Band	2.4GHz ISM Band
Battery	Li polymer rechargeable battery
Battery Life	Offline: approx. 24 hours (depend on usage conditions) Online: approx. 8 hours (depend on usage conditions) Intermittent : depend on usage conditions
Recharge Time	approx. 2 hours
Sampling Frequency	ECG: 125-1kHz, Pulse: 15-125Hz, Acceleration: 15-125Hz, Temperature: 1Hz
External Dimensions	approx. 64(W) X 28(D) X 9.6(H)* mm (* highest point)
Weight	approx. 14.0g (including battery)
Allowable Temperature	Ambient Temperature (Ta): 10 °C ~ 40 °C
Waterproof Property	IPX5 / IPX7