



<Structure>




<Remark>

- Sheet material : FK2
- Sheet thickness : 0.45mm
- ATR material : FK2
- ATR thickness : 0.35 mm
- Wire Type : 0.3mm x 2
- Ts : 13


Top view



Side view



Bottom view



<Thickness>

Coil side Unit: mm

	Typ	Max
Coil+Resin	0.350	0.368
Adhesive tape	0.050	0.053
PET Tape	0.030	0.032
Sheet (FK2)	0.450	0.495
PET Tape	0.030	0.032
Total	0.910	0.978

ATR side Unit: mm

	Typ	Max
PET Tape	0.030	0.032
ATR (FK2)	0.350	0.385
Sheet (FK2)	0.450	0.495
PET Tape	0.030	0.032
Total	0.860	0.943

<Electrical Characteristics>

- Ls [uH] : 11.9 typ @100kHz
- Rs [ohm] : 0.22 typ @100kHz