


LOC	DIST	REVISIONS					
AJ	17	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D2	REVISED PER ECO-11-005030	11MAR11	RK	HMR



RECOMMENDED STRIP LENGTH

- ① CABLE USED WITHOUT SPACER
- ② CABLE USED WITH SPACER
- 3. SEE INSTRUCTION SHEET 408-2798
- 4. PARTS PACKAGED UNASSEMBLED
- ⑤ USE WITH HAND TOOL FRAME 354940-1
- ⑥ USE WITH HANDTOOL 69710-1, OR
PNEUMATIC TOOL 69365 & 69365-3
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ OBSOLETE	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-4	227322-8	9-227074-1	8-5227079-3
	RG-188 DOUBLE BRAID AND RG-316 DOUBLE BRAID	—	58330-1	69477-4	A	—	227194-1	—	9-329049-0	227322-8	9-413530-3	8-5227079-2
	RG-59/U,59A/U AND 59B/U	220217-2	220189-2	220187-2	A	1.090	—	227423-1	9-50428-0	221607-6	9-413530-0	8-5227079-1
	RG-62/U,62A/U AND 62B/U				B							
	RG-58/U,58A/U,58B/U,58C/U, AND 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	221607-5	9-227074-0	8-5227079-0
	BELDEN 88240 AND BERK-TEK BTDC-58	220217-1	220189-1	220187-1	A	1.312	—	—	9-228783-0	221607-5	9-227074-0	7-5227079-5
	RG-62/U,62A/U AND 62B/U	220217-2	220189-2	220187-2	B	1.090	—	227423-1	9-50428-0	9-221607-6	9-413530-0	7-5227079-2
	RG-59/U,59A/U AND 59B/U				A							
BELDEN 89907	—	318452-2	—	A	1.312	—	—	9-228783-0	1-221607-6	9-227074-0	6-5227079-8	
△ OBSOLETE	BELDEN 9907 AND RG-141A/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	1-221607-6	9-227074-0	6-5227079-7
	BELDEN 9290	—	—	220043-1	A	1.490	—	—	9-51713-3	1-221607-6	9-413530-1	6-5227079-5
	BELDEN 9907	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	1-221607-6	9-227074-0	6-5227079-4
△ OBSOLETE	RG-142/U,142A/U, AND 142B/U	220217-1	220189-1	220187-1	A	1.280	—	—	9-225382-0	1-221607-6	9-227074-0	6-5227079-1
	HI TEMP RG-59/U,TIMES PL59 AND PLF59	—	220189-5	—	A	1.312	—	—	9-228784-0	221607-5	9-413530-0	5-5227079-3
△ 2	BELDEN 88240 AND BERK-TEK BTDC-58	220217-1	318452-2	—	A	1.312	—	—	9-228783-0	221607-5	9-227074-0	4-5227079-3
	RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-0	227322-4	9-227074-1	2-5227079-2
	RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-0	9-227322-1	9-413530-3	2-5227079-0
	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	9-329461-0	2-221607-2	9-413530-2	1-5227079-9
	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-0	227322-8	9-227074-1	1-5227079-6
	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	227423-1	9-50428-0	9-221607-6	9-413530-0	1-5227079-1
	RG-62/U,62A/U & 62B/U				B							
	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	9-221607-5	9-227074-0	5227079-9
	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	227423-1	9-50428-0	221607-6	9-227074-2	5227079-7
	RG-62/U,62A/U & 62B/U				B							
RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	9-225382-0	221607-5	9-227074-0	5227079-6	
RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	221607-5	9-227074-0	5227079-5	
	CABLE SIZE	DIE SET △6	DIE SET △5	CRIMP TOOL	VIEW	A	⑤ TUBING QTY=1	④ SPACER QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 29MAR2005 J. HAVENER CHK 29MAR2005 J. HAVENER APVD 29MAR2005 T. LIPPERT		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .016 4 PLC ± - ANGLES ± - FINISH -		NAME - PLUG, COMMERCIAL, BNC -	
		PRODUCT SPEC 108-12044 APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO A1 00779 C=5227079	
MATERIAL -		WEIGHT -		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 OF 1 REV D2	