



TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**



Product Drawings

TE CONNECTIVITY (TE)
PLG ASSY,25 POS,AMPLIMITE
[AMPLIMITE](#) | [AMPLIMITE](#)

206800-1
TE Internal Number: 206800-1
Mil-Spec: 311P409-3P-B-15

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Connector Style **Plug**

Number of Positions **25**

Power/Signal/Coax Combination **No**

Shell Size **3**

Contact Style **Crimp Snap-In**

**AMPLIMITE NONMAGNETIC PLUG ASSEMBLY WITHOUT SIZE 20 PIN
CONTACTS, SERIES 109, SHELL SIZE 3, 25 POSITION**

PDF
English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type Features

Connector Style	Plug
Shell Size	3
Connector & Contact Terminates To	Wire & Cable
Blindmate	No
Product Type	Connector

Configuration Features

Number of Positions	25
Power/Signal/Coax Combination	No

Body Features

Non-Magnetic	Yes
Shell Material	Brass
Shell Plating Material	Gold
Retention Clip Material	Copper Alloy



Contact Features

Contact Style

Crimp Snap-In

Contact Size

20

Contact Mating Area Plating Thickness (µin)

100 – 150

Contact Type

Pin

Contact Mating Area Plating Material

Gold

Contact Base Material

Copper

Mechanical Attachment

Mounting Hole Diameter

3.91 mm [.154 in]

Operation/Application

ULTRA-LITE Connector

No

Packaging Features

Packaging Method

Package


Statement of Compliance

Statement of Compliance
PDF

Compatible Products

> [Contact Product Support](#)

Also in the Series | [AMPLIMITE](#)





Customers Also Bought

CIRCUIT BREAKERS	BOX MOUNT D-SUB CONNECTORS	BOX MOUNT D-SUB CONNECTORS	BOX MOUNT D-SUB CONNECTORS
			
W68-X2Q12-7=M6/M7/M9/W6/W7 W68-X2Q12-7	AMPLIMITE RECEPT ASY, 25 POS 206801-1	PLUG ASSY, 15 POSN, AMPLMTE 206798-1	PLUG ASSY, 37 POSN, AMPLIMITE 206802-1

