




REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN	APVD
	F3	REV PER ECO 18-011576	8-29-18	CT	DM



- TE MATING CONNECTOR PART NUMBER 2226920 MATCHING KEYING AND NUMBER OF POSITIONS.
- SHELL FINISH: SELECTIVE PLATE 7.5µm MIN ZINC-NICKEL OVER 10.0µm MIN ELECTROLESS NICKEL ALL OVER.
- ROHS COMPLIANT.
- MATERIALS: ALUMINUM ALLOY, THERMOPLASTIC AND FLUORSILICONE .
- CONNECTOR SHALL MEET ENVIRONMENTAL REQUIREMENTS PER MIL-STD-810G.
- ASSEMBLY ACCEPTS SIZE 23 PIN CONTACTS.
- CONTACT CURRENT RATING 5 AMPS CRIMPED TO 22 AWG WIRES.
- CONTACT REMOVAL TOOL, GLENAIR PART NUMBER 809-088.
- CONNECTOR SHIPPED WITH DUST CAPS.
- MARKINGS PER MIL-STD-202, METHOD 215.
- CONTACT PINS ARE KITTED IN SEALED PLASTIC BAGS AND SHIPPED UN-ASSEMBLED TO CONNECTOR.
- UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.
- THIS DRAWING HAS UNLIMITEDUSAGE RIGHTS.



GROUND CONTACT
TE P/N 2226913-2
SCALE 5:1
QTY: 2
(ODD DASH NUMBERS ONLY)

SIGNAL CONTACT
TE P/N 2226913-1
SCALE 5:1
QTY: 7
(ODD DASH NUMBERS ONLY)

255	155	ME	7	---	4-2226910-4
255	155	ME	7	11	4-2226910-3
205	105	MD	7	---	4-2226910-2
205	105	MD	7	11	4-2226910-1
245	115	MC	7	---	4-2226910-0
245	115	MC	7	11	3-2226910-9
220	140	MB	7	---	3-2226910-8
220	140	MB	7	11	3-2226910-7
195	165	MA	7	---	3-2226910-6
195	165	MA	7	11	3-2226910-5
210	95	F	7	---	3-2226910-4
210	95	F	7	11	3-2226910-3
275	75	E	7	---	3-2226910-2
275	75	E	7	11	3-2226910-1
275	140	D	7	---	3-2226910-0
275	140	D	7	11	2-2226910-9
210	75	B	7	---	2-2226910-8
210	75	B	7	11	2-2226910-7
210	150	A	7	---	2-2226910-6
210	150	A	7	11	2-2226910-5
230	95	C	7	---	2-2226910-4
230	95	C	7	11	2-2226910-3
255	155	ME	6	---	2-2226910-2
255	155	ME	6	11	2-2226910-1
205	105	MD	6	---	2-2226910-0
205	105	MD	6	11	1-2226910-9
245	115	MC	6	---	1-2226910-8
245	115	MC	6	11	1-2226910-7
220	140	MB	6	---	1-2226910-6
220	140	MB	6	11	1-2226910-5
195	165	MA	6	---	1-2226910-4
195	165	MA	6	11	1-2226910-3
210	95	F	6	---	1-2226910-2
210	95	F	6	11	1-2226910-1
275	75	E	6	---	1-2226910-0
275	75	E	6	11	2226910-9
275	140	D	6	---	2226910-8
275	140	D	6	11	2226910-7
210	75	B	6	---	2226910-6
210	75	B	6	11	2226910-5
210	150	A	6	---	2226910-4
210	150	A	6	11	2226910-3
230	95	C	6	---	2226910-2
230	95	C	6	11	2226910-1
B	A	KEYING	POSITIONS	REMARKS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03FEB2014	TE Connectivity PLUG CONNECTOR ASSEMBLY NETT WARRIOR	
DIMENSIONS:		CHK	07FEB2014		
mm. [INCHES]		C.Y.I			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	07FEB2014		
0 PLC ±		PRODUCT SPEC		NAME	
1 PLC ±		APPLICATION SPEC		SIZE	
2 PLC ±		WEIGHT		CAGE CODE	
3 PLC ±		CUSTOMER DRAWING		DRAWING NO	
4 PLC ±				RESTRICTED TO	
ANGLES				A1	
FINISH				C=2226910	
				SCALE 8:1	
				SHEET 1 OF 1	
				REV F3	