







DIMENSION	TOLERANCE
BELOW 10 mm	± 0.3
10~100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°



P.C.B. LAYOUT



NO.	H	H1	H2
DT002-S11BBB-1	10.70	10.25	8.80

HATCHED AREA SHOW SOLDERING LAND

SPECIFICATION:

- 1.RATING: 30VDC, 0.1A.
- 2.CONTACT RESISTANCE: 1Ω MAX.
- 3.INSULATION RESISTANCE: 100VDC-100MΩ MIN.
- 4.WITHSTAND VOLTAGE: 100VAC-1 MINUTE
- 5.OPERATING FORCE: 35gf MAX.
- 6.LIFE CYCLE: 50,000 CYCLE

DATE	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION	DATE	APPROVAL	DESIGN	UNIT	MODE	DETECT SWITCH
2010/10/27	KAVEN	SCALE	1 : 1	PART	DT002-S11BBB				
2011/02/20	KAVEN	CONFIRM	ALAN	VIEW	DT002-S11BBB				
DATE	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION	DATE	APPROVAL	DESIGN	UNIT	MODE	DETECT SWITCH