



4

3

2

1

3M™ TEXTOL™ QFN TEST AND BURN-IN SOCKET



NOTES:

1. MATERIALS:

SPRINGS	SS	PLATING : Au
CONTACTS	Be Cu	COLOR : BLACK
IC GUIDES	PES	COLOR : BLACK
PRESSURE PAD	PES	COLOR : BLACK
COVER	PPS or equiv.	COLOR : BLACK
BASE	PES	COLOR : BLACK

2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).

3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE:

WWW.3MCONNECTOR.COM PN 216-5205-01

DESIGN REFERENCE		NEXT ASSEMBLY		LDS /ARM	
DESIGNATION	ECO	DATE	ISSUE DATE AND DESCRIPTION	DRAWN	CHKD
0000	ECO	4/2/12	MFG		
0000	L SCHMIDT	DATE	DATE		
0000	0000	DATE	DATE		
DIVISION		DIVISION CODE		TITLE	
DO NOT SCALE DRAWING		SCALE 5		TOLERANCES EXCEPT AS NOTED	
THERMAL ANGLE PROJECTION		INCHES		MILLIMETERS	
ASME Y14.5 - 1994		0 ± .1		0 ± .1	
MAX SURFACE ROUGHNESS 125		200 ± .002		200 ± .002	
DIAL SURFACES		200 ± .002		200 ± .002	
DIMENSIONED ONLY		200 ± .002		200 ± .002	
ANGLES ±		°		°	
CAGE NUMBER		DRAWING NO.		REV.	
78-5100-2518-8		78-5100-2518-8		A	
MODEL		DEF.		SHT	
TEXTOL - QFN		LISTS		1 OF 2	

A

B

C

D

A


B

C




D

DRAWING NUMBER 78-5100-2518-8



REVISION A



FOOTPRINT AS VIEWED LOOKING DOWN FROM TOP OF SOCKET



DETAIL D



DETAIL E

RECOMMENDED IC (REF.)

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[216-5205-01](#)