



OGA DIAGONAL: 13.90 [353.10]
VA DIAGONAL: 13.18 [334.79]
PA DIAGONAL: 12.44 [316.04]





TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8041-203	98-0003-2526-0	FFC	4.27" [108.46]	AG500	23655
17-8041-205	98-0003-3229-0	FFC	8.00" [203.20]	AG500	23655
17-8041-206	98-0003-2527-8	NOV	SEE DWG	AG500	23655
17-8041-221	98-0003-2530-2	SER	4.27" [108.46]	AG500	23655
17-8041-223	98-0003-2531-0	SER	6.00" [152.40]	AG500	23655
17-8041-226	98-0003-3230-8	USB R	8.00" [203.20]	AG500	23655
17-8041-227	98-0003-3231-6	SER	8.00" [203.20]	AG500	23655

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 460±10%
2. NICOMATIC HOUSING P/N: OL05
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHIELD
4	UL
5	UR

UNITS	INCHES [MM]	 3M TOUCH SYSTEMS METHUEN, MA USA © COPYRIGHT 2005 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.
TOLERANCES UNLESS OTHERWISE SPECIFIED		
.X	±	
.XX	±.03 [.76]	
.XXX	±.015 [.38]	
ANGLES	±1°	
THIRD ANGLE PROJECTION		
DO NOT SCALE DRAWING		
SCALE	1 = 1	

DRAWN K. CROWLEY 9/05

REV	CHANGE NOTICE	DATE	DRW
F	REVISED PER CO 033533	9/11	SB
05	REVISED PER CO 030452	5/09	SEB
04	REVISED PER CO 030072	3/09	MTD

TITLE			
MARKETING DRAWING SCT32NN 13.18"			
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
C	28265-MKT	F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[98-0003-32290](#)