


OGA DIAGONAL: 23.09 [586.4]
VA DIAGONAL: 22.37 [568.2]
PA DIAGONAL: 21.08 [535.5]

TOP LEVEL NUMBER	US NUMBER	TYPE	DM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9311-205	98-0003-2209-3	FFC	8.00" [203.20]	AG500	23655
17-9311-206	98-0003-2731-6	NOV	SEE DWG	AG500	23655
17-9311-227	98-0003-2734-0	SER	8.00" [203.20]	AG500	23655
17-9311-226	98-0003-3052-6	USB R	8.00" [203.20]	AG500	23655
N/A	98-0003-3652-3	HID D	8.00" [203.20]	AG500	23655
N/A	98-0003-3420-5	FFC	8.00" [203.20]	WC100	34523
N/A	98-0003-3418-9	SER	8.00" [203.20]	WC100	34523
N/A	98-0003-3419-7	USB R	8.00" [203.20]	WC100	34523
N/A	98-0003-3975-8	DUAL	8.00" [203.20]	AG500	23655



- NOTES:
1. WEIGHT OF GLASS IN GRAMS: 1196±10%
2. NICOMATIC HOUSING P/N: QLO5
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	UL
2	UR
3	SHLD
4	LR
5	LL

UNITS	INCHES [MM]	
TOLERANCES UNLESS OTHERWISE SPECIFIED		
.X	$\pm$	
.XX	$\pm .03$	[.76]
.XXX	$\pm .015$	[.38]
ANGLES	$\pm 1^\circ$	
THIRD ANGLE PROJECTION		
DO NOT SCALE DRAWING		
SCALE	1 = 1	

3M 3M TOUCH SYSTEMS
METHUEN, MA
USA

© COPYRIGHT 2004
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN	AH	4/07
-------	----	------

K	REVISE PER CO 036256	4/13	SB
J	REVISE PER CO 034069	1/12	SB
H	REVISE PER CO 033640	10/11	SB
REV	CHANGE NOTICE	DATE	DRW

TITLE	MARKETING DRAWING		
THE	SCT32NN 22.37" W		
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE C	DOCUMENT NO. 34079-MKT	REV K	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[98-0003-2209-3](#) [98-0003-2734-0](#) [98-0003-3052-6](#)