

3M™ Locator Plate 3443-117

Instructions


1.0 General

The Locator Plate 3443-117 is designed for the assembly of the following Euro (DIN 41 612 type) connectors, two-piece (adhesive) version:

62C64 - xxx - xx

62C96 - xxx - xx

62B64 - xxx - xx



Note: This locator plate can only be used with press platen 3442-9, which must be ordered separately.

2.0 Assembly Procedure

- 2.1 Adjust press shut height.
- 2.2 Install press platen 3442-9.
- 2.3 Install locator plate.
- 2.4 Cut required cable length.
- 2.5 Remove adhesive liner.
- 2.6 Place cable correctly into connector cover.
- 2.7 Place cover with cable onto the connector body.
- 2.8 Place the connector cover down into the correct groove.
- 2.9 Assemble by lowering the press handle.
- 2.10 Raise press handle and remove the finished assembly.
- 2.11 Visually inspect the harness to ensure that the cover is fully locked and cable alignment is correct. The latch should be flush with the end of the connector (at both ends) and the cover should be flush with the rear face of the flange at both ends.

Customer and Technical Service

Within the U.S.:

Customer Service: 800-225-5373

Technical Support: 512-984-6703

Outside of the U.S.:

For customer service and technical support, please contact your local 3M Electronic Solutions Division representative.

3M is a trademark of 3M Company.

Important Notice

PRODUCT USE: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's application.

Warranty; Limited Remedy; Limited Liability.

3M's product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



**Electronic Solutions Division
Interconnect Products**

6801 River Place Blvd.
Austin, TX 78726-9000
800-225-5373
www.3Mconnectors.com

Please recycle. Printed in USA.
© 3M 2011
78-9101-4656-8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)
[3443-117](#)