

OGA DIAGONAL: 14.03 [356.4]  
VA DIAGONAL: 13.28 [337.2]  
PA DIAGONAL: 12.53 [318.3]

| TOP LEVEL NUMBER | US NUMBER      | CHINA NUMBER   | TYPE  | DIM "A" (TOTAL GLASS TO CONNECTOR) | A/G FINISH | PROD SPEC |
|------------------|----------------|----------------|-------|------------------------------------|------------|-----------|
| 17-9581-203      | 98-0003-2259-8 | N/A            | FFC   | 4.27" [108.46]                     | AG500      | 23655     |
| 17-9581-218      | 98-0003-2263-0 | N/A            | USB R | 4.27" [108.46]                     | AG500      | 23655     |
| 17-9581-205      | 98-0003-3232-4 | 59-0000-0210-1 | FFC   | 8.00" [203.20]                     | AG500      | 23655     |
| 17-9581-226      | 98-0003-3233-2 | 59-0000-0211-9 | USB R | 8.00" [203.20]                     | AG500      | 23655     |
| 17-9581-227      | 98-0003-3234-0 | 59-0000-0212-7 | SER   | 8.00" [203.20]                     | AG500      | 23655     |

ESD CLAMSHELL  
CASE IS USED WITH  
ALL NOV, USB AND  
SER TERMINATIONS.





(FFC)

(USB R)

EXII-7760UC  
98-0003-2814-0  
USB CONTROLLER  
SOLDER SIDE

(SER)

EXII-7720SC  
98-0003-2217-6  
SERIAL CONTROLLER  
SOLDER SIDE



| PINOUT |      |
|--------|------|
| 1      | LL   |
| 2      | UL   |
| 3      | SHLD |
| 4      | UR   |
| 5      | LR   |

#### NOTES:

1. WEIGHT OF GLASS IN GRAMS: 461±10%
2. NICOMATIC HOUSING P/N: OL05  
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12  
HOUSING ORIENTED WITH LATCH DOWN

| UNITS INCHES [MM]                     |  |
|---------------------------------------|--|
| TOLERANCES UNLESS OTHERWISE SPECIFIED |  |
| .X ±                                  |  |
| .XX ±.03 [.76]                        |  |
| .XXX ±.015 [.38]                      |  |
| ANGLES ±1°                            |  |
| THIRD ANGLE PROJECTION                |  |
| DO NOT SCALE DRAWING                  |  |
| SCALE 1 = 1                           |  |



3M TOUCH SYSTEMS  
METHUEN, MA  
USA  
© COPYRIGHT 2004  
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE  
3M COMPANY AND MAY NOT BE REPRODUCED  
WITHOUT 3M WRITTEN PERMISSION OR USED OR  
DISCLOSED FOR OTHER THAN 3M AUTHORIZED  
PURPOSES.

DRAWN A. Hartofelis 9/08

|                    |                        |              |     |
|--------------------|------------------------|--------------|-----|
| D                  | REVISED PER CO 034264  | 2/12         | SB  |
| C                  | REVISE PER CO 033640   | 10/11        | SB  |
| 03                 | REVISED PER CO 030452  | 6/09         | SB  |
| REV                | CHANGE NOTICE          | DATE         | DRW |
| TITLE              |                        |              |     |
| MARKETING DRAWING  |                        |              |     |
| SCT32NN 13.28"     |                        |              |     |
| CAD FORMAT AUTOCAD |                        | SHEET 1 OF 1 |     |
| SIZE C             | DOCUMENT NO. 36186-MKT | REV D        |     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[98-0003-3232-4](#) [98-0003-3233-2](#) [98-0003-3234-0](#)