

3M™ Butyl Mastic Tape 2212

Mastic Sealant for Cold Weather Conditions

Data Sheet

July 2010

Description 3M™ Butyl Mastic Tape 2212 is a high tack, self-fusing butyl rubber mastic ideal for making water and humidity resistant seals. Butyl Mastic Tape 2212 may be overwrapped with vinyl tape to create a reliable weatherproof seal around cable connections and other weather-sensitive devices.

Agency Approvals & Self Certifications Meets the requirements of:

RoHS 2002/95/EC



RoHS Compliant 2002/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2002/618/EC, unless the substance is in an application that is exempt under RoHS. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

Applications Butyl Mastic Tape 2212 is a high tack sealant with excellent adhesion to cable jackets and other insulating materials. It maintains its tack and flexibility to temperatures as low as 0°F (-18°C), ensuring a high quality seal over a wide range of temperatures. It may be overwrapped with vinyl tape to create a weatherproof seal with excellent resistance to environmental factors such as water, condensation, dust, UV and sunlight over a range of temperatures.

Typical Properties Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

Physical Properties (Test Method)	Typical Value US units (metric)
Color	Black
Adhesion to Steel (ASTM D-3330)	35 oz/in (3,8 N/cm)
Tack , (3M TM 286B) 73°F (23 °C) 0°F (-18 °C)	25 lbs/in ² (0,17 Mpa) 15 lbs/in ² (0,10 Mpa)
Water Absorption 24 hrs (ASTM D-570)	0.07%
Water Vapor Trans. Rate (ASTM F-1249)	0.13 g/100 in ² 24h (2,0 g/m ² 24h)
Flex (ASTM C-765) -9°F (-23 °C)	Pass
Cone Penetration (ASTM D-217)	3.1 in (80 mm)

3M™ Butyl Mastic Tape 2212

Shelf Life & Storage	3M™ Butyl Mastic Tape 2212 has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).
---------------------------------	---

Availability	Please contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1-800-245-3573.
---------------------	---

Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
-------------------------	---

Warranty; Limited Remedy; Limited Liability	This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.
--	---

3M is a trademark of 3M Company.



Electrical Markets Division
6801 River Place Boulevard
Austin, TX 78726-9000
800.245.3573
Fax: 800.245.0329
www.3M.com/electrical

Please recycle
© 3M 2010 All rights reserved
78-8129-9362-0 Rev A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)
[7010399907](#)