



OGA DIAGONAL: 31.48 [799.7]  
VA DIAGONAL: 30.09 [764.4]  
PA DIAGONAL: 28.37 [720.5]


US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
98-0003-3481-7	FFC	8.00" [203.20]	AG500	23655
98-0003-3480-9	SER	8.00" [203.20]	AG500	23655
98-0003-3479-1	USB-R	8.00" [203.20]	AG500	23655



ESD CLAMPSHELL  
CASE IS USED WITH ALL  
NOV, USB AND SER  
TERMINATIONS.

(USB-R)  
EXII-7769UC  
98-0003-2815-7  
USB CONTROLLER  
SOLDER SIDE

(SER)  
EXII-7720SC  
98-0003-2217-6  
SERIAL CONTROLLER  
SOLDER SIDE



1.47±.020 [3.73±.51]  
TOTAL THICKNESS  
OF GLASS, CABLE  
AND STRAIN RELIEF

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 2214±10%
2. NICOMATIC HOUSING P/N: OLOS
3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
4. HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
X	± .03 [1.76]
.XX	± .015 [1.38]
.XXX	± .01 [1.38]
ANGLES	± 1°

3M TOUCH SYSTEMS  
3M TOUCH, MA  
USA  
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE  
3M COMPANY. NO PART OF THIS DOCUMENT MAY BE  
REPRODUCED OR TRANSMITTED IN ANY FORM OR BY  
ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT  
PERMISSION IN WRITING FROM THE 3M COMPANY.

REV	DESCRIPTION	DATE	BY
B	REVISED PER CO 034264	2/12	SB
01	RELEASE PER CO 030786	8/09	AH

MARKETING DRAWING  
SCT32NN 30.09" W

DO NOT SCALE DRAWING	SCALE	1 = 1
DO NOT SCALE DRAWING	SCALE	1 = 1

37298-MKT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[98-0003-2815-7](#)