

# Scotch® Stretchable Tape

8884 • 8886



## Technical Data

June, 2009

### Product Description

Scotch® Stretchable Tape 8884 and 8886 are a high-performance transparent stretchable tape, designed to contain A- and B-type pallets for internal and external shipping purposes.\*\*

\*\* A-type pallets have less than one inch overhang.

B-type pallets have between one and three inches of overhang.

### Construction

	Backing	Adhesive	Backing Color
<b>Scotch® Tape 8884</b>	4 mil (0.102 mm) Linear Low Density Polyethylene	Pressure sensitive synthetic rubber resin	Clear
<b>Scotch® Tape 8886</b>	6 mil (0.152 mm) Linear Low Density Polyethylene	Pressure sensitive synthetic rubber resin	Clear

### Typical Physical Properties

**Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.**

	Scotch® Tape 8884	Scotch® Tape 8886	ASTM Test Method
Adhesion to Steel:	70 oz./in. width (77 N/100 mm width)	65 oz./in. width (71 N/100 mm width)	D-3330
Tensile Strength:	20 lbs./in. (350 N/100 mm)	28 lbs./in. (490 N/100 mm)	D-3759
Elongation at Break:	710%	720%	D-3759
Total Thickness:	5 mil (0.13 mm)	7 mil (0.18 mm)	D-3652

### Available Sizes

	Scotch® Tape 8884	Scotch® Tape 8886
Standard Widths:	1.4 in. (36 mm)	1.4 in. (36 mm)
Core Size (ID):	3 in. (76.2 mm)	3 in. (76.2 mm)
Lengths:	60 yds. (55 m)	60 yds. (55 m) and 547 yds. (500 m)

### Storage Conditions

Store behind present stock. Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40-50% relative humidity are recommended. Rotate your stock.

### Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

# Scotch® Stretchable Tape

8884 • 8886

---

## Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

---

## Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

---

## Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

---

## Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

---

**ISO 9001:2000**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



### Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
[www.3M.com/industrial](http://www.3M.com/industrial)



*Recycled Paper*  
40% pre-consumer  
10% post-consumer

Scotch is a registered trademark of 3M.  
Printed in U.S.A.  
©3M 2009 70-0710-0216-9 (6/09)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)  
[8886](#)