

# 3M™ Heat Shrink Tubing HDT

## Heavy-Duty, Polyolefin

Data Sheet

November 2018

### Description

3M™ Heat Shrink Tubing HDT is designed to provide reliable performance as well as excellent mechanical and environmental protection. This flame-retardant product combines the important advantage of easy handling and installation with maximum operating reliability and system protection. The tubing comes with a factory-applied sealant. This sealant is a heat-activated thermoplastic material that remains soft and flexible over long periods under adverse environmental conditions. During heating the sealant softens, bonds to underlying surfaces and fills small voids that might be present.

When cool, the sealant forms a barrier against water, moisture, dirt and other environmental contaminants. Heavy-duty tubing is fabricated from specially formulated cross-linked polyolefin, assuring long-term environmental protection. The tubing is also highly chemical, abrasive and split resistant.

The tubing is rated for continuous operation at -55°C (-67°F) to 110°C (230°F). Minimum shrink temperature is 121°C (250°F). Uncoated product (without sealant) is available on special order.

### Agency Approvals & Self Certifications

Meets the requirements of: AS23053/15, Class 1\*

For RoHS and REACH information, please visit [www.3M.com/regs](http://www.3M.com/regs)

\*Formerly MIL-I-23053/15, MIL-DTL-23053/15 and SAE-AMS-DTL-23053/15

### Standard Sizes and Dimensions (without adhesive)

3M Part Number	Cable Range	Expanded I.D. (Minimum) in. (mm)	Recovered I.D. (Minimum) in. (mm)	Recovered Outer Wall Thickness (Nominal) in. (mm)	Length in.	Std. Pkg. Pieces/ Carton	Color
HDT-0300-48A	#14 - #8 AWG	.30 (7,62)	.10 (2,5)	.08 (2,0)	48	20	Red and Black
HDT-0400-48A	#12 - #6 AWG	.40 (10,2)	.15 (3,8)	.09 (2,3)	48	20	Red and Black
HDT-0800-48A	#8 - 1/0 AWG	.80 (20,3)	.20 (5,1)	.11 (2,8)	48	20	Red and Black
HDT-1100-48A	#2 - 4/0 AWG	1.10 (27,9)	.37 (9,4)	.12 (3,0)	48	20	Red and Black
HDT-1500-48A	3/0 - 400 MCM	1.50 (38,1)	.50 (12,7)	.17 (4,3)	48	20	Black Only
HDT-2000-48A	250 - 750 MCM	2.00 (50,8)	.65 (16,5)	.17 (4,3)	48	10	Black Only
HDT-3000-48A	600 - 1250 MCM	3.00 (76,2)	1.00 (25,4)	.17 (4,3)	48	10	Black Only
HDT-4500-48A	1500 - 2500 MCM	4.50 (114,3)	1.50 (38,1)	.17 (4,3)	48	5	Black Only
HDT-6000-48A	2.1" - 4.8" O.D.	6.00 (152,4)	1.80 (45,7)	.17 (4,3)	48	5	Black Only
HDT-7000-48A	2.5" - 5.6" O.D.	7.00 (177,8)	2.00 (50,8)	.17 (4,3)	48	5	Black Only

# 3M™ Heat Shrink Tubing HDT

---

**Shrink Ratio** 3M™ Heat Shrink Tubing HDT has a 3:1 shrink ratio. When freely recovered, the tubing will be 33.3% of its as supplied diameter. The recovered wall thickness is proportionate to the degree of recovery.

---

**Applications** Can be used as cable sleeve, flame retardant, polyolefin for 1 kV or other long term environmental protection – highly chemical, abrasion and split resistant

---

**Typical Properties** Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

---

Physical Properties	Typical Value US units (metric)
Tensile Strength	2400 psi
Ultimate Elongation	475%
Longitudinal Change	+1, -10%
Secant Modulus	14,000 psi
Specific Gravity	1.28
*Heat Aging 7 Days @ 175°C (347°F)	Elongation 225%
*Heat Shock 4 hrs @ 225°C (437°F)	No dripping, cracking, flowing
*Low Temperature Flexibility 4 hrs. @ -55°C (-67°F)	No cracking
Flammability	Self-extinguish

\*Outer wall only.

Electrical Properties	Typical Value US units (metric)
Dielectric Strength	500 V/mil (60 mils)
Volume Resistivity	10 <sup>14</sup> ohm-cm

Chemical Properties	Typical Value US units (metric)
Corrosion Effect	Non-corrosive
Solvent Resistance Tensile Strength Dielectric Strength	1500 psi 200 v/mil
Water Absorption	0.02%
Fungus Resistance	Non-nutrient

# 3M™ Heat Shrink Tubing HDT

---

## Shelf Life & Storage

3M™ Heat Shrink Tubing HDT has a 10-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).

---

## Availability

Please contact your local distributor; available from [3M.com/electrical](http://3M.com/electrical) [Where to Buy] or call 1.800.245.3573.

Order this tubing by product name, size equivalent to the expanded inside diameter, package type and color. Always order the largest size that will shrink snugly over the component to be covered.

Example: HDT-1100-48A Tubing, 4 ft., Black

---

3M is a trademark of 3M Company.

---

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

---

## Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

---



## Electrical Markets Division

Austin, TX  
800.245.3573  
FAX: 800 245 0329  
[www.3M.com/electrical](http://www.3M.com/electrical)

Please recycle  
© 3M 2018 All rights reserved  
78-8129-9333-1 C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[HDT1100-48A-RD](#) [HDT0800-48A-RD](#)