



Dual Lock™ Reclosable Fastener SJ3550

Product Data Sheet

January 2017

Supersedes: October 2016

Product Description

3M™ Dual Lock™ Reclosable Fastener SJ3550 is a general purpose black reclosable fastener with 250 stems per square inch. This black fastener has mushroom shaped stems on a polypropylene carrier, which is coated with a white, general purpose acrylic pressure sensitive adhesive.

Key Features

- General purpose acrylic adhesive bonds to medium to high surface energy substrates (e.g. metal, ABS)
- Stem density: 250 stems/in²
- Closure cycle life > 1 000
- Mushroom shaped stems snap in place to ensure fastener is engaged
- Good aging performance and resistance against humidity
- Good initial adhesion
- Quick and easy to install
- Durable for indoor and outdoor applications

Physical Properties

Type	SJ3550
Adhesive Type	Acrylic adhesive
Tape Colour	White
Backing	Black polypropylene
Stems	Black polypropylene
Release Liner	3M branded filmic liner
Engaged Thickness acc. DIN EN 1942: 2008	5.4 mm

Performance Characteristics

Type	SJ3550
90 ° Peel adhesion to Stainless Steel acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	25 N/cm
90 ° Peel adhesion to PP acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	4 N/cm
90 ° Peel adhesion to ABS acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	30 N/cm
90 ° Peel adhesion to Stainless Steel acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell and after 10d @ 38 °C & 98 % rH	23 N/cm
Dyn. Tensile Engagement Strength acc. to ASTM D897-08, tested @ RT	113 N/in ²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ RT	231 N/in ²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ 70 °C	56 kPa
Dynamic Shear – Max. Force acc. ISO 29863:2007 to stainless steel	102 kPa
Dynamic Shear – Elongation acc. ISO 29863:2007 to stainless steel	60 %
Static Shear Strength Stainless Steel ISO 29863:2007, after 72h @ RT dwell (Holds minimum 77.5 g/cm ² for 10.000 minutes)	23 °C – 500 g 70 °C – 500 g
„T“ Peel (flexible to flexible) acc. ISO 29862:2007	53 N/cm

Storage & Shelf Life

Store at 16 °C – 25 °C and 40 – 65 % relative humidity in its original box. The product can be stored up to 24 months after production.

Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity.

For Additional Information

To request additional product information or to arrange for sales assistance, call.....
Address correspondence to: 3M

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

3M United Kingdom PLC
2M Centre, Cain Road, Bracknell
RG12 8HT
United Kingdom

3M Svenska AB
Herrjärva torg 4
170 67 Solna
Sweden

3M Eesti OÜ
Pärnu mnt. 158
11317 Tallinn
Estonia

3M Ireland Ltd
The Iveagh Building, 3rd Floor
The Park, Carrickmines 18
Ireland

3M a/s
Hannemanns Allé 53
DK-2300 Copenhagen S.
Denmark

3M Latvia SIA
K.Ulmaņa gatve 5
Rīga, LV-1004
Latvia

3M Belgium bvba/sprl
Hermeslaan 7
1831 Diegem
Belgium

3M Norge AS
Tærudgata 16
2004 Lillestrøm
Norway

3M Lietuva UAB
A.Goštauto g. 40
Vilnius LT- 03163
Lithuania

3M Nederland B.V.
Molengraaffsingel 29
2629 JD Delft
The Netherlands

Suomen 3M Oy
Keilaranta 6
02150 Espoo
Finland

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)
[SJ3460](#)