

SPEC# \_\_\_\_\_

QUANTITY \_\_\_\_\_

application: **MULTIPLE EQUIPMENT**

models:

## High Flow Series Cyst Replacement Cartridges

3M™ Water Filtration Products line of cyst reduction replacement cartridges offer multiple solutions to help improve the taste, appearance and consistency of your product at flow rates from 1 gpm up to 5 gpm

### PRODUCT BENEFITS

- Sanitary Quick Change (SQC) encapsulated cartridge design reduces media contamination during change-outs.
- Expansive breadth of product offering that can accommodate most applications.
- Multiple choice of medias to help provide solutions for varying water conditions.
- Certified by NSF to Standard 53 for cyst<sup>1</sup> reduction.
- FDA CFR-21 compliant materials.
- NSF certified; 3M Purification: Commercial Modular-High Flow Series.
- Contains, Integrated Pre-Activated Carbon Technology ("I.M.P.A.C.T.") media HF40 series thru HF90 series only excluding HF90-S-SR, HF90-S-SR5.

### PRODUCT SPECIFICATIONS

Model No.	Part No	3M ID#	Micron Rating	Claims	Flow Rate	Capacity
HF90	5613503	70020020155	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, Chlorine Taste & Odor, Turbidity, Cyst <sup>1</sup>	5 gpm (18.9 lpm)	54,000 gals. (204,412 lit.)
HF90-S	5613505	70020020163	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, Chlorine Taste & Odor, Turbidity, Cyst <sup>1</sup> , Scale Inhibitor <sup>3</sup>	5 gpm (18.9 lpm)	54,000 gals. (204,412 lit.)
HF90-S-SR	5617105	70020020767	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, cyst <sup>1</sup> , Scale Inhibitor <sup>3</sup>	5 gpm (18.9 lpm)	N/A
HF90-S-SR5	5617107	70020020775	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, cyst <sup>1</sup> , scale inhibitor <sup>3</sup>	5 gpm (18.9 lpm)	N/A
HF60	5613403	70020020122	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup>	3.34 gpm (12.6 lpm)	35,000 gals. (132,489 lit.)
HF60-S	5613405	70020116706	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , Scale Inhibitor <sup>3</sup>	3.34 gpm (12.6 lpm)	35,000 gals. (132,489 lit.)
HF40	5613303	70020020114	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup>	2.1 gpm (7.9 lpm)	25,000 gals. (94,635 lit.)
HF40-S	5613305	70020121417	0.2	Bacteria <sup>2</sup> , Bacteriostatic, Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , Scale Inhibitor <sup>3</sup>	2.1 gpm (7.9 lpm)	25,000 gals. (94,635 lit.)
HF30	5615105	70020020577	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup>	1.67 gpm (6.3 lpm)	14,000 gals. (52,996 lit.)
HF30-S	5615107	70020020585	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , Scale Inhibitor <sup>3</sup>	1.67 gpm (6.3 lpm)	14,000 gals. (52,996 lit.)
HF30-MS	5615111	70020020601	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , proprietary Scale Inhibitor blend <sup>3</sup>	1.67 gpm (6.3 lpm)	14,000 gals. (52,996 lit.)
HF20	5615101	70020020551	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup>	1.5 gpm (5.7 lpm)	9,000 gals. (34,069 lit.)
HF20-S	5615103	70020020569	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , Scale Inhibitor <sup>3</sup>	1.5 gpm (5.7 lpm)	9,000 gals. (34,069 lit.)
HF20-MS	5615109	70020020593	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , Scale Inhibitor blend <sup>3</sup>	1.5 gpm (5.7 lpm)	9,000 gals. (34,069 lit.)
HF10-MS	5609329	70020019595	0.5	Particulate, Chlorine Taste & Odor, Cyst <sup>1</sup> , Scale Inhibitor blend <sup>3</sup>	1.0 gpm (3.8 lpm)	3,500 gals. (13,249 lit.)

<sup>1</sup>Based on the use of Cryptosporidium parvum oocysts.

<sup>2</sup>As tested with E.Coli ATCC (11229). As tested and verified by manufacturer's laboratory.

<sup>3</sup>As tested and verified by manufacturer's laboratory.

# Cyst Replacement Cartridges

SPEC# \_\_\_\_\_

QUANTITY \_\_\_\_\_

MODEL NUMBER \_\_\_\_\_

PART NUMBER \_\_\_\_\_

Model No.	Part No	Shipping Dimension	Weight	Case Qty
HF90	5613503	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs. (2.3 kg.)	1
HF90-S	5613505	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)"	5 lbs. (2.3 kg.)	1
HF90-S-SR	5617105	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs. (2.3 kg.)	1
HF90-S-SR5	5617107	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs. (2.3 kg.)	1
HF60	5613403	22" x 4-7/8" x 4-7/8" (55.9 cm. x 12.4 cm. x 12.4 cm)	3.4 lbs. (1.5 kg.)	1
HF60-S	5613405	22" x 4-7/8" x 4-7/8" (55.9 cm. x 12.4 cm. x 12.4 cm)	3.4 lbs. (1.5 kg.)	1
HF40	5613303	10-1/2" x 5-1/2" x 23-1/4" (26.7 cm. x 14 cm. x 59.1 cm)	5 lbs. (2.3 kg.)	2
HF40-S	5613305	10-1/2" x 5-1/2" x 23-1/4" (26.7 cm. x 14 cm. x 59.1 cm)	5 lbs. (2.3 kg.)	2
HF30	5615105	10-1/2" x 10-1/2" x 28-1/4" (26.7 cm. x 26.7 cm. x 71.8 cm)	9 lbs. (4.1 kg.)	4
HF30-S	5615107	10-1/2" x 10-1/2" x 28-1/4" (26.7 cm. x 26.7 cm. x 71.8 cm)	"9 lbs. (4.1 kg.)"	4
HF30-MS	5615111	10-1/2" x 10-1/2" x 28-1/4" (26.7 cm. x 26.7 cm. x 71.8 cm)	9 lbs. (4.1 kg.)	4
HF20	5615101	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	"10 lbs. (4.5 kg.)"	6
HF20-S	5615103	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF20-MS	5615109	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF10-MS	5609329	20-3/8" x 10-1/2" x 15-3/4" (51.8 cm. x 26.7 cm. x 40.0 cm)	10 lbs. (4.5 kg.)	8

## LIMITED WARRANTY

3M Purification Inc. warrants this Product will be free from defects in material and manufacture for one (1) year from the date of purchase: This warranty does not cover failures resulting from abuse, misuse, alteration or damage not caused by 3M Purification Inc. or failure to follow installation and use instructions. No warranty is given as to the service life of any filter cartridge or membrane as it will vary with local water conditions and water consumption. **3M PURIFICATION INC. MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR USAGE OF TRADE.** If the Product fails to satisfy this Limited Warranty during the warranty period, 3M Purification Inc. will replace the Product or refund your Product purchase price. This warranty does not cover labor. **The remedy stated in this paragraph is Customer's sole remedy and 3M Purification Inc.'s exclusive obligation. For additional information, see the entire Limited Warranty located in the product Installation and Operating Instruction Manual.**

**Limitation of Liability.** 3M Purification Inc. will not be liable for any loss or damage arising from this 3M Purification Inc. product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states and countries do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.

# 3M™ Water Filtration Products

## SPECIFICATIONS

- Maximum operating pressure of 125 psi (862 kPa) and operating temperature of 100° (37.8°C).
- Materials are FDA CFR-21 Compliant.
- Shipping weight: Refer to Price Book
- Operating weight: Contact factory

## IMPORTANT: INSTALLATION TIPS

**These installation tips are for informational purposes only and are not intended to be used as actual installation instructions.**

**⚠ WARNING: To reduce the risk associated with the ingestion of contaminants:**

- **Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.** Systems certified for cyst reduction may be used on disinfected water that contain filterable cysts. EPA Establishment #070595-CT-001.

**CAUTION: To reduce the risk associated with property damage due to water leakage:**

- **Read and follow** Use Instructions before installation and use of this system.
- Installation and use **MUST** comply with all state and local plumbing codes.
- **Protect from freezing**, remove filter cartridge when temperatures are expected to drop below 40°F (4.4°C).
- **Do not install on hot water supply lines.** The maximum operating water temperature of this filter system is 100°F (37.8°C).
- **Do not install** if water pressure exceeds 125 psi (862 kPa). If your water pressure exceeds 80 psi (552 kPa), you must install a pressure limiting valve. Contact a plumbing professional if you are uncertain how to check your water pressure.
- **Do not install** where water hammer conditions may occur. If water hammer conditions exist you must install a water hammer arrester. Contact a plumbing professional if you are uncertain how to check for this condition.
- The disposable filter cartridge **MUST** be replaced every twelve (12) months, at the rated capacity or sooner if a noticeable reduction in flow rate occurs.



3M Purification Inc.  
400 Research Parkway  
Meriden, CT 06450 U.S.A.  
Toll Free: 1-866-990-9785  
Worldwide: 203-237-5541  
Fax: 203-238-8977  
www.3Mfoodservice.com • 3Mpurification.com

3M is a trademark of 3M Company.  
© 2013 3M Company. All rights reserved.  
70020303148 REV 0513

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000001667](#) [7000001672](#) [7000001675](#) [7000001752](#) [7000042826](#) [7000050413](#) [7100053657](#) [7100090103](#)