

High Temperature Fine Line Tape

4737S • 4737T

Technical Data

August, 2011

Product Description Scotch® High Temperature Fine Line Tape 4737 is a vinyl paint masking tape for fascia, rocker panels, two-tone and other multiple color applications where critical paint break lines are required.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Vinyl	Rubber	Scotch® Tape 4737S - Blue (Solid) Scotch® Tape 4737T - Blue (Translucent)	36 yds. (32.9 m)

Typical Physical Properties **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

		ASTM Test Method
Adhesion to Steel:	10.5 oz./in. width (11.5 N/100 mm)	D-3330
Tensile Strength:	16 lbs./in. width (280 N/100 mm)	D-3759
Elongation at Break:	115%	D-3759
Tape Thickness:	5.4 mils (0.137 mm)	D-3652
Temperature Use Range:	Up to 300°F (149°C) for up to 30 minutes.*	

*Has been laboratory tested on stainless steel and found to leave little to no adhesive residue at bake temperatures of up to 300°F (149°C) for 30 minutes. The actual temperature and time performance may be higher or lower for a given application and can vary due to substrate coatings and processing conditions (i.e. multiple bake cycles and the temperature of the surface at removal). We suggest testing the product under your process conditions to determine if it meets your needs.

Features

- The conformable backing is designed for uniform stretching to help create better paint lines.
- The adhesive and backing work together to minimize paint seepage.
- Outstanding fine line color separation.
- Smooth trimmed edges create a continuous straight paint line.
- Designed for indoor use.
- Vinyl backing is heat resistant for one piece removal.
- Functions with high temperature paint bake cycles.
- Minimal neck down when stretched for accurate paint lines.
- Scotch® Tape 4737S - Solid backing aids in seeing contrast with substrate color.
- Scotch® Tape 4737T – Translucent backing allows visual confirmation of adhesive wet out on substrate.
- Conformable to allow ease of application in areas of tight radii and depressions.

Scotch® High Temperature Fine Line Tape

4737S • 4737T

Application Ideas	Ideal for the transportation OEM industry for paint masking of metal and plastic surfaces.
Storage	Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.
Shelf Life	To obtain best performance, use this product within one year from date of manufacture.
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2008

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Scotch is a registered trademark of 3M.
Printed in U.S.A.
©3M 2011 70070951036 (8/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[4737S-1x36](#) [4737S-3/4x36](#)