




Scotchlok™ Connectors

MVU18PC, MVU14PC, MVU10PC

Parallel Connector, Vinyl Insulated, Butted Seam



Data Sheet

Product Number	Wire Range (AWG)	L	Thickness	Barrel I.D.		Maximum Insulation Diameter
				In	CMA	
MVU18PC	22-18	0.67	0.030	0.070	4900	0.145
MVU14PC	16-14	0.67	0.030	0.090	8100	0.170
MVU10PC	12-10	0.87	0.040	0.135	18225	0.250

MVU18PC

1 #22 to 1 #22, 20, 18, 16

1 #20 to 1 #20, 18, 16

1 #18 to 1 #18

Min. CMA: 1280, Max. CMA: 3600

MVU14PC

1 #22 to 1 #22, 20, 18, 16, 14

1 #20 to 1 #20, 18, 16, 14

1 #18 to 1 #18, 16, 14

1 #16 to 1 #16

Min. CMA: 1280, Max. CMA: 5730

MVU10PC

1 #18 to 1 #18, 16, 14, 12, 10

1 #16 to 1 #16, 14, 12, 10

1 #14 to 1 #14, 12

Min. CMA: 3240, Max. CMA: 12860


Installation Information

⚠ WARNING

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

Strip away the end 3/8 inch of wire insulation.

Make the crimp in the proper station of a recommended 3M crimp tool: TH-440, TH-450 (scissor style) or TR-490 (ratchet style) hand tools.



Wire Insertion

Specifications

Wire Size:

See Table Above

Barrel Seam:

Butted

Maximum Operating Temp:

221°F (105°C)

Maximum Current:

Same as Wire

Insulator Material:

Vinyl

Terminal Material:

ETP Copper

Terminal Plating:

Tin

Engineering Specification

Crimp-type terminals shall, electrically and mechanically, connect permanently to the pre-stripped end of two stranded copper wires.

The connector line shall offer barrel variations in wire (AWG) size (22 thru 4) and construction (non-insulated brazed seam, vinyl insulated butted seam, nylon insulated seamless, etc...).

The Vinyl Insulated, Butted Seam Parallel Connector shall be tin-plated, annealed copper, having a round barrel and a close fitting vinyl covering, color coded and sized for a specified (AWG) wire range (22-18, 16-14, 12-10).

3M and Scotchlok are trademarks of 3M

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
<http://www.3M.com/elpd>

Litho in USA.
© 3M 2002 78-8126-0617-2-A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MVU18PCK](#) [MVU14PCK](#) [MVU10PCK](#)