



# Premium Matte Cloth (Gaffers) Tape GT

## Technical Data

November 2017

**Product Description** 3M™ Premium Matte Cloth (Gaffers) Tape utilizes a cotton cloth backing with a synthetic rubber adhesive system for use in high strength and highly conformable applications.

Construction	Backing	Adhesive	Color	Roll Length	Standard Widths
	Cotton Cloth	Synthetic Rubber	19 Colors Available	50 m (54.6 yards)	GT1 24mm (0.94 in) GT2 48mm (1.88 in) GT3 72mm (2.83 in)

## Typical Physical Properties

**Note:** The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	72 oz./in. width (78.8 N/100 mm width)	D-3330
Tensile Strength:	56 lbs./in. width (980 N/100 mm width)	D-3759
Elongation at Break:	6%	D-3759
Tape Thickness:	11 mils (0.27 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C) for up to 30 min. Removes cleanly*	

\* Has been laboratory tested on painted steel panels and found to remove cleanly at bake temperatures of up to 200°F (93°C) for 30 minutes. The actual temperature and time performance may be higher or lower for a given application. Clean removal can vary dependent on surface type, processing conditions such as multiple bakes, type of paint involved as well as the temperature of the surface at removal. We recommend testing the product under your conditions to determine if it meets your needs.

## Features

- Synthetic rubber adhesive provides good adhesion to various substrates and removes cleanly.
- Matte cloth backing provides high strength and conformability to irregular surfaces
- Tears easily by hand and provides ease of application and handling.
- 19 distinctive colors make it easy to label and identify areas that need high visibility
- Good quick stick.

# 3M™ Premium Matte Cloth (Gaffers) Tape GT

Application Ideas	<ul style="list-style-type: none"><li>• Bundling, holding, splicing and marking.</li><li>• Low light reflectance backing for entertainment and video productions.</li><li>• Labeling applications where an easy to identify tape is needed.</li></ul>
Storage	Store under normal conditions of 60°F to 80°F (16°C to 21°C) and 40 to 60% R.H. in the original carton.
Shelf Life	To obtain best performance, use this product within one year from date of manufacture.
Technical Information	The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.
Product Selection and Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.
Warranty, Limited Remedy, and Disclaimer	Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a quality system registered to ISO 9001 standards.



## Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
[www.3M.com/industrial](http://www.3M.com/industrial)

3M is a trademark of 3M Company.  
Printed in U.S.A.  
©3M 2017 (11/17)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7010300508](#) [7010312513](#) [7010312514](#) [7010336127](#) [7010336128](#) [7010336129](#) [7010336130](#) [7010336131](#)  
[7010336132](#) [7010376453](#) [7010376454](#) [7010376455](#) [7010376456](#) [7010376457](#) [7010376458](#) [7010376459](#)  
[7010376460](#) [7100171413](#)