

# 3M™ Water Filtration Products

SPEC# \_\_\_\_\_

QUANTITY \_\_\_\_\_

application: **MULTIPLE EQUIPMENT**

models:

## High Flow Series Replacement Cartridges HF45-S-SR5 thru HF95



3M™ Water Filtration Products line of replacement cartridges offer multiple solutions to help improve the taste, appearance and consistency of your product at flow rates from 2.1 gpm to 7 gpm.

### PRODUCT BENEFITS

- Sanitary Quick Change (SQC) encapsulated cartridge design reduces media contamination during change-outs.
- Expansive breadth of product offering that can accommodate most applications.
- Multiple choice of medias to help provide solutions for varying water conditions.
- FDA CRF-21 compliant materials.
- NSF Certified; 3M Purification Inc: Commercial Modular-High Flow Series<sup>1</sup>, Components-Commercial Modular<sup>2</sup>.
- Contains Integrated Pre-Activated Carbon Technology ("I.M.P.A.C.T.") media.

### PRODUCT SPECIFICATIONS

Model No.	Part No	3M ID#	Micron Rating	Claims	Flow Rate	Capacity
HF95 <sup>1</sup>	5613507	70020020171	3	Particulate*, Chlorine Taste & Odor	5 gpm (18.9 lpm)	54,000 gals. (204,412 lit.)
HF95-S <sup>1</sup>	5613509	70020121433	3	Particulate*, Chlorine Taste & Odor, Scale Inhibitor*	5 gpm (18.9 lpm)	54,000 gals. (204,412 lit.)
HF95-S-SR <sup>2</sup>	5613527	70020300458	5	Particulate*, Scale Inhibitor*, Fits Standard (A3) Keyed heads	7 gpm (26.5 lpm)	N/A
HF95-S-SR5 <sup>2</sup>	5613525	70020300441	5	Particulate*, Scale Inhibitor*, Fits Black (A5) Keyed heads	7 gpm (26.5 lpm)	N/A
HF65 <sup>1</sup>	5613407	70020115476	3	Particulate*, Chlorine Taste & Odor	3.34 gpm (12.6 lpm)	35,000 gals. (132,489 lit.)
HF65-S <sup>1</sup>	5613409	70020020130	3	Particulate*, Chlorine Taste & Odor, Scale Inhibitor*	3.34 gpm (12.6 lpm)	35,000 gals. (132,489 lit.)
HF65-S-SR <sup>2</sup>	5613453	70020300425	5	Particulate*, Scale Inhibitor*, Fits Standard (A3) Keyed heads	5 gpm (18.9 lpm)	N/A
HF65-S-SR5 <sup>2</sup>	5613451	70020300417	5	Particulate*, Scale Inhibitor*, Fits Black (A5) Keyed heads	5 gpm (18.9 lpm)	N/A
HF45 <sup>1</sup>	5613307	70020115468	3	Particulate*, Chlorine Taste & Odor	2.1 gpm (7.9 lpm)	25,000 gals. (94,635 lit.)
HF45-S <sup>1</sup>	5613309	70020121425	3	Particulate*, Chlorine Taste & Odor, Scale Inhibitor*	2.1 gpm (7.9 lpm)	25,000 gals. (94,635 lit.)
HF45-S-SR <sup>2</sup>	5613346	70020300409	5	Particulate*, Scale Inhibitor*, Fits Standard (A3) Keyed heads	3.5 gpm (13.2 lpm)	N/A
HF45-S-SR5 <sup>2</sup>	5613344	70020300391	5	Particulate*, Scale Inhibitor*, Fits Black (A5) Keyed heads	3.5 gpm (13.2 lpm)	N/A

\*As tested and verified by manufacturer's laboratory.



# Replacement Cartridges

SPEC# \_\_\_\_\_  
 QUANTITY \_\_\_\_\_  
 MODEL NUMBER \_\_\_\_\_  
 PART NUMBER \_\_\_\_\_

# 3M™ Water Filtration Products

## SPECIFICATIONS

- Maximum operating pressure of 125 psi (862 kPa) and operating temperature of 100° (37.8°C).
- Materials are FDA CFR-21 compliant.
- Shipping weight: Refer to Price Book
- Operating weight: Contact factory

## IMPORTANT: INSTALLATION TIPS

**These installation tips are for informational purposes only and are not intended to be used as actual installation instructions.**

**⚠ WARNING: To reduce the risk associated with the ingestion of contaminants:**

- **Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.**

**CAUTION: To reduce the risk associated with property damage due to water leakage:**

- **Read and follow** Use Instructions before installation and use of this system.
- Installation and use **MUST** comply with all state and local plumbing codes.
- **Protect from freezing**, remove filter cartridge when temperatures are expected to drop below 40°F (4.4°C).
- **Do not install on hot water supply lines.** The maximum operating water temperature of this filter system is 100°F (37.8°C).
- **Do not install** if water pressure exceeds 125 psi (862 kPa). If your water pressure exceeds 80 psi (552 kPa), you must install a pressure limiting valve. Contact a plumbing professional if you are uncertain how to check your water pressure.
- **Do not install** where water hammer conditions may occur. If water hammer conditions exist you must install a water hammer arrester. Contact a plumbing professional if you are uncertain how to check for this condition.
- The disposable filter cartridge **MUST** be replaced every twelve (12) months, at the rated capacity or sooner if a noticeable reduction in flow rate occurs.

Model No.	Part No.	Shipping Dimension	Weight	Case Qty
HF95	5613507	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs.(2.3 kg.)	1
HF95-S	5613509	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs. (2.3 kg.)	1
HF95-S-SR	5613527	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs.(2.3 kg.)	1
HF95-S-SR5	5613525	28" x 4-7/8" x 4-7/8" (71.1 cm. x 12.4 cm. x 12.4 cm)	5 lbs.(2.3 kg.)	1
HF65	5613407	22" x 4-7/8" x 4-7/8" (55.9 cm. x 12.4 cm. x 12.4 cm)	3.4 lbs. (1.5 kg.)	1
HF65-S	5613409	22" x 4-7/8" x 4-7/8" (55.9 cm. x 12.4 cm. x 12.4 cm)	3.4 lbs. (1.5 kg.)	1
HF65-S-SR	5613453	22" x 4-7/8" x 4-7/8" (55.9 cm. x 12.4 cm. x 12.4 cm)	3.4 lbs. (1.5 kg.)	1
HF65-S-SR5	5613451	22" x 4-7/8" x 4-7/8" (55.9 cm. x 12.4 cm. x 12.4 cm)	3.4 lbs. (1.5 kg.)	1
HF45	5613307	10-1/2" x 5-1/2" x 23-1/4" (26.7 cm. x 14 cm. x 59.1 cm)	5 lbs. (2.3 kg.)	2
HF45-S	5613309	10-1/2" x 5-1/2" x 23-1/4" (26.7 cm. x 14 cm. x 59.1 cm)	5 lbs. (2.3 kg.)	2
HF45-S-SR	5613346	10-1/2" x 5-1/2" x 23-1/4" (26.7 cm. x 14 cm. x 59.1 cm)	5 lbs. (2.3 kg.)	2
HF45-S-SR5	5613344	10-1/2" x 5-1/2" x 23-1/4" (26.7 cm. x 14 cm. x 59.1 cm)	5 lbs. (2.3 kg.)	2

## LIMITED WARRANTY

3M Purification Inc. warrants this Product will be free from defects in material and manufacture for one (1) years from the date of purchase: This warranty does not cover failures resulting from abuse, misuse, alteration or damage not caused by 3M Purification Inc. or failure to follow installation and use instructions. No warranty is given as to the service life of any filter cartridge or membrane as it will vary with local water conditions and water consumption. **3M PURIFICATION INC. MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR USAGE OF TRADE.** If the Product fails to satisfy this Limited Warranty during the warranty period, 3M Purification Inc. will replace the Product or refund your Product purchase price. This warranty does not cover labor. **The remedy stated in this paragraph is Customer's sole remedy and 3M Purification Inc.'s exclusive obligation. For additional information, see the entire Limited Warranty located in the product Installation and Operating Instruction Manual.**

**Limitation of Liability.** 3M Purification Inc. will not be liable for any loss or damage arising from this 3M Purification Inc. product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states and countries do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.



3M Purification Inc.  
 400 Research Parkway  
 Meriden, CT 06450 U.S.A.  
 Toll Free: 1-866-990-9785  
 Worldwide: 203-237-5541  
 Fax: 203-238-8701  
 www.3Mfoodservice.com • 3Mpurification.com

3M is a trademark of 3M Company.  
 © 2013 3M Company. All rights reserved.  
 70020303130 REV 0513

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000001669](#) [7000050410](#) [7000050884](#) [7000050885](#) [7000051728](#) [7010314367](#) [7010340307](#) [7010382784](#)  
[7010382785](#) [7100006231](#)