

Product Description

3M™ Stainless Steel Cleaner and Protector is a streak-free, fast drying formula specifically designed for stainless steel and certain other metal surfaces. Scotchgard™ technology from 3M provides a protective barrier, making fingerprints, permanent marker, food soils such as mustard, bleach stains, urine, and toothpaste easier to clean. Treated stainless has a natural, streak-free appearance. The product is dispensed as a water thin, colorless liquid.

Special Features

- Cleans and protects in one step
- Leaves no greasy build-up on surfaces
- Allows spot cleaning of stainless surfaces without altering appearance
- Reduces the time needed to spot clean stainless surfaces compared to other cleaners and polishes tested
- Reduces the amount of product consumed to clean stainless surfaces compared to other cleaners and polishes tested
- No fragrance or dye added
- Ready-to-use formula
- Leaves a Scotchgard™ protective barrier
- Reduces corrosion on stainless steel surfaces exposed to HCl
- Slows resoiling/dust pickup
- Reduces fingerprinting
- Dries streak free
- Dries faster than other stainless steel cleaners and polishes tested
- 100% water based-no mineral oil formulation
- Over 90% reduction in carbon compared to other cleaners and polishes tested
- NSF® A7 Certified-safe for use on non-food contact surfaces.
- U.S. Patent Pending

Applications

- Suitable for use on stainless steel, chrome, architectural aluminum, and other interior metal surfaces

Packaging

- 1 quart (946 ml) bottle
- 6 one quart bottles per case



This product meets Green Seal Standards™ GS-52 and GS-53 based on effective performance, minimized/recycled packaging, and protective limits on VOCs and human & environmental toxicity. GreenSeal.org.



Quick Links

[Resource Library](#)
[Safety Data Sheets \(SDS\)](#)
[Video Library](#)

Some of these links lead to web-based resources that are not product-specific.

General Use Directions

1. Spray 3M™ Stainless Cleaner and Protector directly onto the surface or dispense onto a Scotch-Brite™ High Performance Cloth or other form of clean wiping pad such as a paper towel.
2. Wipe the surface until it is clean and dry.
3. If using a squeegee, apply the cleaner to the surface, and squeegee downward while surface is wet.
4. If surface has been previously treated with an oil based product, refer to the stripping and cleaning guide for instruction on removal.

Disposal recommendations

Dispose of contents/container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. Dispose of waste product in a permitted industrial waste facility. Empty and clean product containers may be disposed as non-hazardous waste and/or recycled.

Consult your specific regulations and service providers to determine available options and requirements

Improper Use: Improper use of this product constitutes not using the product according to manufacturer instructions or directions, such as those listed above.

Note: Refer to product Safety Data Sheet for specific physical properties, health hazard, first aid and precautionary information.

Improper use of product may increase risk of health effects.

3M™ Stainless Steel Cleaner and Protector:

- 33-8784-2

3M™ Stainless Steel Cleaner and Protector Ready-to-Use

Health and Safety

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to [3M.com/SDS](https://www.3m.com/SDS), or by mail or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501. When using any equipment, always follow the manufacturers' instructions for safe operation.

Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the **Customer Service Department at 1-800-852-9722**.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

Commercial Solutions Division

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-328-0033
[3M.com/Facility](https://www.3m.com/Facility)

© 3M 2018. All rights reserved.
3M and Scotchgard are trademarks of 3M.
Used under license in Canada.
All other trademarks are property of their respective owners.
Revision B, March 2018. Please recycle.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7100082687](#)