





3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS




NOTES:

1. MATERIALS:
- | | | |
|--------------|---------------|---------------|
| SPRINGS | SS | |
| CONTACTS | Be Cu | PLATING : Au |
| IC GUIDES | PES | COLOR : BLACK |
| PRESSURE PAD | PES | COLOR : BLACK |
| COVER | PPS or equiv. | COLOR : BLACK |
| BASE | PES | COLOR : BLACK |
2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).
3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE: WWW.3MCONNECTOR.COM PN 252-4205-00

DESIGN REFERENCE				NEXT ASSEMBLY				A 37213 INITIAL RELEASE				ARM							
DISTRIBUTION CODES								REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT		CHKD	
														DATE		MFG		DATE	
														DATE		APPVL		DATE	
DIVISION				DIVISION CODE								3M Center St. Paul, MN 55144				© 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.			
DO NOT SCALE DRAWING		SCALE 5 1		TOLERANCES EXCEPT AS NOTED				TITLE QFN TEST SOCKET 0.4mm, 52 POS., 6X6 PKG, EVEN ROW NO TP											
		THIRD ANGLE PROJECTION		INCHES .0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002															
				MILLIMETERS 0 ± .1 .0 ± .02 .00 ± .005 0.00 ± .0002															
INTERPRET PER ASME Y14.5 - 1994						CAGE NUMBER		SIZE 		DRAWING NO. 78-5100-2445-4				REV. A					
MAX SURFACE ROUGHNESS 125 		☐ ALL SURFACES ☒ MARKED ONLY				ANGLES ± 1°		MODEL TEXTTOOL - QFN				DET. LISTS		☐ YES ☒ NO		SHT 1 OF 2			

3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



DESIGN REFERENCE				NEXT ASSEMBLY				REV	ECO	ISSUE DATE AND DESCRIPTION				DRFT	CHKD
DISTRIBUTION CODES								DRFT		DATE		MFG		DATE	
								CHKD		DATE		APPVL		DATE	
DIVISION				DIVISION CODE				3M 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING		SCALE 5 1		TOLERANCES EXCEPT AS NOTED											
				INCHES				TITLE QFN TEST SOCKET 0.4mm 52 POS, 6X6 PKG, EVEN ROW NO TP							
				.0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002											
THIRD ANGLE PROJECTION				MILLIMETERS				CAGE NUMBER SIZE DRAWING NO. REV.							
INTERPRET PER ASME Y14.5 - 1994				0 ± .1 .0 ± .005 .00 ± .0002											
MAX SURFACE ROUGHNESS 125 ✓ ☐ ALL SURFACES ☒ MARKED ONLY				ANGLES ± 1°				78-5100-2445-4							
								MODEL TEXTTOOL - QFN				DET. LISTS ☐ YES ☒ NO		SHT 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[252-4205-00](#)