




Scotchlok™ Terminals

MV8BC, MV6BC, MV4BC

Butt Connector, Vinyl Insulated, Brazed Seam



Data Sheet

September, 2007

Product Number	Wire Range (AWG)	L	Thickness	Barrel Length	Barrel I.D.	Maximum Insulation Diameter
MV8BC	8	1.50	0.050	0.38	0.175	.30
MV6BC	6	1.71	0.050	0.47	0.250	.40
MV4BC	4	2.17	0.075	0.53	0.280	.48

Specifications

Wire Size:	See Table Above
Barrel Seam:	Brazed
Maximum Current:	Same as Wire
Insulator Material:	Vinyl
Terminal Material:	ETP Copper
Terminal Plating:	Tin

Regulatory Agencies



UL Listed as a Wire Connector, tested per UL Standard 486C, UL File No. E23438.

Maximum Operating Temperature:	221°F (105°C)
Maximum Voltage Rating:	600 volts max building wire 1000 volts max signs and fixtures

CSA Certified – CSA Standard 22.2, No. 0.65, CSA File No. LR 22190.

Maximum Operating Temperature:	221°F (105°C)
Maximum Voltage Rating:	600 volts max building wire 1000 volts max signs and fixtures

Installation Information

WARNING

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end of wire insulation ½ inch for 8 AWG, 9/16 inch for 6 AWG and 5/8 inch for 4 AWG.

Make the crimp the proper station of a recommended 3M™ Crimp Tool: TH-450 (for 8 and 6 AWG); T&B WT-117A, die sets 11822, 8; 11823, 6; 11824, 4.



● Barrel Crimp (Required)

Engineering Specification

Crimp-type terminals shall, electrically and mechanically, connect permanently to a pre-stripped end of a stranded copper wire.

The connector line shall offer barrel variations in wire (AWG) size (22-18, 16-14, 12-10) and construction (non-insulated brazed seam, vinyl insulated butted seam, nylon insulated seamless, etc.). The connector line shall have regulatory agency coverage (UL Listing, CSA Certification). The connectors shall be marked with the wire and manufacturer's symbol (↑).

The vinyl insulated brazed seam butt connector shall be tin plated, annealed copper, having a double-length, round brazed seam barrel with a center stop, covered by a molded vinyl sleeve, color coded and sized for a specified (AWG) wire range (8, 6, 4).

Insulated connectors shall be UL Listed and CSA Certified for 600 volts maximum, building wire: 1000 volts maximum signs or lighting fixtures (luminaires), and temperature rated 221°F (105°C) maximum.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability:

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

3M and Scotchlok are trademarks of 3M Company.

3M
Electrical Markets Division
6801 River Place Blvd.
Austin, TX 78726-9000
800/245-3573
FAX 800-245-0329

Please recycle. Printed in U.S.A.
© 3M 2007 All rights reserved.
78-8125-9666-2_B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MV8BCK\(BULK\)](#)