



**Science.  
Applied to Life.™**

# Barricade Tapes for the Electrical Industry

**Identify and limit access  
to hazardous areas with  
Scotch® Barricade Tapes  
from 3M.**

Use Scotch® Barricade Tapes for notification of restricted access to hazardous areas or to manage access to work sites. The Scotch® Barricade Tapes can also be used to warn pedestrian traffic of danger or communicate your safety message. Whether you need above ground, buried, detectable or environmentally friendly materials, 3M has a barricade tape to meet your marking requirements.



# Scotch® Barricade Tapes







## 300 Series

Scotch® Barricade Tapes 300 Series are not only effective but economical as well. One roll has sufficient length to designate a large area. The above ground barricade tape rolls are 3" wide, while the buried barricade tape rolls are available in both 3" and 6" widths. The tapes are constructed of durable polyethylene plastic that is designed to help prevent tearing. Bold two-inch black characters on bright backgrounds are designed to attract attention and provide a warning message that is clearly visible. The 300 Series tapes are available in various lengths, thicknesses and with different warning messages.




3M Prod. Number	Description	Dimension	Background	Legend
-----------------	-------------	-----------	------------	--------



### Scotch® Barricade Tapes (2 mil)

300	Scotch® Barricade Tape 300 CAUTION, Yellow	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Yellow	Caution
301	Scotch® Barricade Tape 301 CAUTION, Yellow	3 in. x 300 ft. x 0.002 in. (7.6 cm x 91.4 m x 0.051 mm)	Yellow	Caution 
356	Scotch® Barricade Tape 356 DANGER, Red	3 in. x 300 ft. x 0.002 in. (7.6 cm x 91.4 m x 0.051 mm)	Red	Danger 
357	Scotch® Barricade Tape 357 DANGER, Red	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Red	Danger
358	Scotch® Barricade Tape 358 CAUTION HIGH VOLTAGE, Yellow	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Yellow	Caution High Voltage 
361	Scotch® Barricade Tape 361 CAUTION DO NOT ENTER, Yellow	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Yellow	Caution Do Not Enter
362	Scotch® Barricade Tape 362 DANGER DO NOT ENTER, Red	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Red	Danger Do Not Enter 
374	Scotch® Barricade Tape 374 CAUTION DO NOT ENTER, Yellow	3 in. x 300 ft. x 0.002 in. (7.6 cm x 91.4 m x 0.051 mm)	Yellow	Caution Do Not Enter
381	Scotch® Barricade Tape 381 DANGER PELIGRO, Red	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Red	Danger Peligro 
382	Scotch® Barricade Tape 382 CAUTION CUIDADO, Yellow	3 in. x 1000 ft. x 0.002 in. (7.6 cm x 304.8 m x 0.051 mm)	Yellow	Caution Cuidado 

### Scotch® Barricade Tapes (3 mil)








330	Scotch® Barricade Tape 330 CAUTION, Yellow	3 in. x 1000 ft. x 0.003 in. (7.6 cm x 304.8 m x 0.076 mm)	Yellow	Caution
331	Scotch® Barricade Tape 331 DANGER, Red	3 in. x 1000 ft. x 0.003 in. (7.6 cm x 304.8 m x 0.076 mm)	Red	Danger 
333	Scotch® Barricade Tape 333 CAUTION DO NOT ENTER, Yellow	3 in. x 1000 ft. x 0.003 in. (7.6 cm x 304.8 m x 0.051 mm)	Yellow	Caution Do Not Enter

### Scotch® Buried Barricade Tapes (4 mil)

302	Scotch® Buried Barricade Tape 302 CAUTION BURIED ELECTRIC LINE, Red	3 in. x 1000 ft. x 0.004 in. (7.6 cm x 304.8 m x 0.102 mm)	Red	Caution Buried Electric Line Below
303	Scotch® Buried Barricade Tape 303 CAUTION BURIED ELECTRIC LINE BELOW, Red	3 in. x 300 ft. x 0.004 in. (7.6 cm x 91.4 m x 0.102 mm)	Red	Caution Buried Electric Line Below 
363	Scotch® Buried Barricade Tape 363 CAUTION HIGH VOLTAGE CABLE BURIED BELOW, Red	3 in. x 1000 ft. x 0.004 in. (7.6 cm x 304.8 m x 0.102 mm)	Red	Caution High Voltage Cable Buried Below 

3M Prod. Number	Description	Dimension	Background	Legend
-----------------	-------------	-----------	------------	--------

### Scotch® Buried Barricade Tapes (cont.)

364	Scotch® Buried Barricade Tape 364 CAUTION BURIED ELECTRIC LINE BELOW, Yellow	3 in. x 1000 ft. x 0.004 in. (7.6 cm x 304.8 m x 0.102 mm)	Yellow	Caution Buried Electric Line Below 
365	Scotch® Buried Barricade Tape 365 CAUTION BURIED FIBER OPTIC LINE BELOW, Orange	3 in. x 1000 ft. x 0.004 in. (7.6 cm x 304.8 m x 0.102 mm)	Orange	Caution Buried Fiber Optic Line Below 
366	Scotch® Buried Barricade Tape 366 CAUTION BURIED CABLE TV LINE BELOW, Orange	3 in. x 1000 ft. x 0.004 in. (7.6 cm x 304.8 m x 0.102 mm)	Orange	Caution Buried TV Line Below 
367	Scotch® Buried Barricade Tape 367 CAUTION BURIED TELEPHONE LINE BELOW, Orange	3 in. x 1000 ft. x 0.004 in. (7.6 cm x 304.8 m x 0.102 mm)	Orange	Caution Buried Telephone Line Below 
368	Scotch® Buried Barricade Tape 368 CAUTION BURIED ELECTRIC LINE BELOW, Red	6 in. x 1000 ft. x 0.004 in. (15.2 cm x 304.8 m x 0.102 mm)	Red	Caution Buried Electric Line Below
369	Scotch® Buried Barricade Tape 369 CAUTION HIGH VOLTAGE CABLE BURIED BELOW, Red	6 in. x 1000 ft. x 0.004 in. (15.2 cm x 304.8 m x 0.102 mm)	Red	Caution High Voltage Cable Buried Below 
370	Scotch® Buried Barricade Tape 370 CAUTION BURIED ELECTRIC LINE BELOW, Yellow	6 in. x 1000 ft. x 0.004 in. (15.2 cm x 304.8 m x 0.102 mm)	Yellow	Caution Buried Electric Line Below 
371	Scotch® Buried Barricade Tape 371 CAUTION BURIED FIBER OPTIC LINE BELOW, Orange	6 in. x 1000 ft. x 0.004 in. (15.2 cm x 304.8 m x 0.102 mm)	Orange	Caution Buried Fiber Optic Line Below 



## Scotch® Detectable Buried Barricade Tapes 400 Series

Scotch® Detectable Buried Barricade Tapes 400 Series are designed for accurately locating and helping prevent damage to valuable underground utility installations. The tapes have an aluminum backing that helps make underground assets easier to find when using a non-ferrous locator. Properly installed, these tapes may help avoid catastrophic accidents caused by inaccurate digging. Locate utilities such as electrical lines and communication cables before you dig.

### Scotch® Buried Barricade Tapes (5 mil)

3M Prod. Number	Description	Dimension	Background	Legend
406	Scotch® Detectable Buried Barricade Tape 406 CAUTION BURIED ELECTRIC LINE BELOW, Red	3 in. x 1000 ft. x 0.005 in. (7.6 cm x 304.8 m x 0.127 mm)	Red	Caution Buried Electric Line Below
407	Scotch® Detectable Buried Barricade Tape 407 CAUTION BURIED FIBER OPTIC LINE BELOW, Orange	3 in. x 1000 ft. x 0.005 in. (7.6 cm x 304.8 m x 0.127 mm)	Orange	Caution Buried Fiber Optic Line Below
408	Scotch® Detectable Buried Barricade Tape 408 CAUTION BURIED ELECTRIC LINE BELOW, Red	6 in. x 1000 ft. x 0.005 in. (15.2 cm x 304.8 m x 0.127 mm)	Red	Caution Buried Electric Line Below
409	Scotch® Detectable Buried Barricade Tape 409 CAUTION BURIED FIBER OPTIC LINE BELOW, Orange	6 in. x 1000 ft. x 0.005 in. (15.2 cm x 304.8 m x 0.127 mm)	Orange	Caution Buried Fiber Optic Line Below
410	Scotch® Detectable Buried Barricade Tape 410 CAUTION BURIED TELEPHONE LINE BELOW, Orange	3 in. x 1000 ft. x 0.005 in. (7.6 cm x 304.8 m x 0.127 mm)	Orange	Caution Buried Telephone Line Below
411	Scotch® Detectable Buried Barricade Tape 411 CAUTION BURIED TELEPHONE LINE BELOW, Orange	6 in. x 1000 ft. x 0.005 in. (15.2 cm x 304.8 m x 0.127 mm)	Orange	Caution Buried Telephone Line Below
412	Scotch® Detectable Buried Barricade Tape 412 CAUTION BURIED HIGH VOLTAGE CABLE BELOW, Red	3 in. x 1000 ft. x 0.005 in. (7.6 cm x 304.8 m x 0.127 mm)	Red	Caution Buried High Voltage Cable Below
413	Scotch® Detectable Buried Barricade Tape 413 CAUTION BURIED HIGH VOLTAGE CABLE BELOW, Red	6 in. x 1000 ft. x 0.005 in. (15.2 cm x 304.8 m x 0.127 mm)	Red	Caution Buried High Voltage Cable Below



# Scotch® Repulpable Barricade Tapes 500 Series

Made of tightly woven cotton fibers, these reusable tapes are an excellent alternative to standard barricade tapes for areas where plastics are undesirable. The Scotch® Barricade Tapes 500 Series is appropriate for indoor applications and recycling areas. These non-conductive tapes are supplied on rolls that measure 3" wide by 150' long.



## Scotch® Repulpable Barricade Tapes (10 mil)

3M Prod. Number	Description	Dimension	Background	Legend
515	Scotch® Repulpable Barricade Tape 515 DANGER, Red	3 in. x 150 ft. (7.6 cm x 45.7 m)	Red	Danger
516	Scotch® Repulpable Barricade Tape 516 CAUTION, Yellow	3 in. x 150 ft. (7.6 cm x 45.7 m)	Yellow	Caution

3M and Scotch are trademarks of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division  
6801 River Place Blvd.  
Austin, TX 78726-9000 USA

Phone 1-800-245-3573  
Web 3M.com/electrical

Please recycle. Printed in USA.  
© 3M 2017. All rights reserved.  
80-6016-0370-9 (08145)XX-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[357](#) [362](#)